

8.5mm FL Ultra High Resolution Fixed Focal Length Lenses



#68-684



Stock **#68-682** 3-4 DAYS

[Similar Products](#)

- 1 +

€1.640,00

ADD TO CART

Qty 1+
€1.640,00

Volume Pricing
[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
96.5

Iris Option:
Variable

Length (mm):
56.00

Horizontal Field of View, 1/2" Sensor: 96.5mm - 40.8°
Filter Thread: M34 x0.50
Maximum Diameter (mm): 36.0
Weight (g): 115.00
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 8.50
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/22
Maximum Distortion (%): <0.31%
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)