

900µm Aperture Diameter, Mounted, Precision Pinhole



900µm Aperture Diameter, Mounted, Precision Pinhole, #56-290

Stock **#56-290** 3-4 DAYS



1



€75,00

ADD TO CART

Qty 1-5

€75,00

Qty 6+

€66,20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Mounted

Outer Diameter (mm):
25 +0.4/-0.000

Construction:
Stainless Steel

Fixed Aperture Diameter (μm): 900
Thickness (mm): 0.03 Nominal
Aperture Tolerance (μm): ±5
Mount Thickness (mm): 1.25 ±0.05
Aperture Centration (μm): ±125

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant