

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Sapphire and Ruby Ball Lenses

Stock #63-227 □ In Stock



1



€76,50

ADD TO CART

Qty 1-10

€76,50

Qty 11+

€60,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.53

Substrate: ☐
Sapphire (Al₂O₃)

Coating:
Uncoated

Type: Ball Lens
Wavelength Range (nm): 200 - 5500
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C): 8.4
Index of Refraction n _d : 1.77
Melting Temperature (°C): 2053.00
Porosity (%): 0.00
Specific Gravity (g/cm³): 3.98
Sphericity (µm): 0.625
Wavelength Range (µm): 0.2 - 5.5
Compressive Strength (psi): 300,000
Diameter Tolerance (µm): ±2.54

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant