


TECHSPEC® 9mm Diameter x -9 FL, VIS-NIR Coated, Plano-Concave Lens



TECHSPEC VIS-NIR Coated Plano-Concave (PCV) Lenses



Stock **#45-913** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

€42,50

ADD TO CART

Qty 1-9

€42,50

Qty 10+

€38,25

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm): -9.00
Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: VIS-NIR (400-1000nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -10.21
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.25
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 8.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 3.63
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R ₁ (mm): -7.07
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View