

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



#59-978 (sensor sold separately)

Stock #59-978 3-4 DAYS



1



€1.055,00

ADD TO CART

Qty 1+

€1.055,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Model Number:
1098297

Length (mm):
193.00

Operating Temperature (°C):
+5 to +40

Resolution:
0.1% of Full Scale (10s Scale)

Type: Power Only
Width (mm): 117.00
Weight (kg): 0.8
Depth (mm): 46
Power Supply: 100-240 V AC, 50/60 Hz OR 2 9V alkaline batteries
Storage Temperature (°C): -20 to +70
Display Accuracy (%): ±1
Calibration Uncertainty (%): ±1.0
Analog Output: 0 to 2 V
Power Sampling Rate (Hz): 20

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View