

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #43-579 3-4 DAYS



1



€330,00

ADD TO CART

Qty 1-5

€330,00

Qty 6+

€264,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Minor Axis (mm):
57.15

Major Axis (mm):
80.82

Surface Flatness (P-V):
λ/8

Substrate: ☐ BOROFLOAT®
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.79
Dimensional Tolerance (inches): ±0.031
Coating Specification: R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Clear Aperture CA (mm): 51.44 (Minor Axis) 72.75 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 15.88
Thickness Tolerance (inches): ±0.060
Thickness Tolerance (mm): ±1.52
Type: Flat Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant