

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Infrared (IR) Right Angle Prisms

Stock #25-040 3-4 DAYS



1



€1.180,00

ADD TO CART

Qty 1+

€1.180,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

Germanium (Ge)

Surface Quality:

60-40

Type:

Right Angle Prism
Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85.00
Length of Hypotenuse (mm): 18.00
Length of Legs (mm): 12.70
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 2000 - 14000
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 2λ
Model Number: GE-RP-12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View