

Infiniprobe N-32 UV Right Angle Video Microscope

See More by [Infinity Photo-Optical Company](#)



Stock **#62-854** [CONTACT US](#)

- 1 + **€3.625,00**

ADD TO CART

Qty 1+
€3.625,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
100.00

Horizontal Field of View, 1/2" Sensor:
2.0mm

Horizontal Field of View, 2/3" Sensor:
2.75mm

Maximum Diameter (mm):
78.5

Weight (g):

181.4
Type: Long Distance Microscope
Primary Magnification PMAG: 0X - 3.2X
Maximum Sensor Format: 2/3"
Working Distance (mm): 32 - ∞
Mount: C-Mount
Style: UV, Right Angle

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
