

Mounted M22.5 x 0.5 Threaded - Green Filter



Stock #46-540 3-4 DAYS

⊖ 1 ⊕ **€47,50**

ADD TO CART

Qty 1-9
€47,50
Qty 10+
€44,10
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
18.5

Filter Thread:
M22.5 x 0.50

Color:
Green

Cut-Off Wavelength (nm):

550.00
Cut-On Wavelength (nm): 520.00
Glass/Filter Number: G-533
Index of Refraction n_d: 1.54
Note: AR Coating: MgF ₂
Outer Diameter (mm): 24.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.0
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.0
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya G-533 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View