



SCHOTT BG38, 50mm Sq., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-417** ☐ In Stock

-

1

+

€88,00

ADD TO CART

Qty 1-10
€88,00
Qty 11+
€78,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Center Wavelength CWL (nm):
470.00

Density (g/cm³): 2.66
Glass/Filter Number: SCHOTT BG38
Length (mm): 50.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n _d : 1.53
Surface Quality: 60-40
Transformation Temperature (°C): 482
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: VIS
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View