

➤



Stock **#46-085** 3-4 DAYS

1

€79,00

ADD TO CART

€79,00

€70,00

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
25.0 x 25.0

Center Wavelength CWL (nm):

360.00
Density (g/cm³): 2.74
Full Width-Half Max FWHM (nm): 45.00
Glass/Filter Number: Hoya U360
Substrate: ☐ Colored Glass
Length (mm): 25.00
Coating: Uncoated
Color: Black
Surface Quality: 80-50
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: UV
Width (mm): 25.00
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View