

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #86-463 [CONTACT US](#)



1



€6.150,00

ADD TO CART

Qty 1+

€6.150,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
≥4.0

Substrate:
[Fused Silica](#) (Corning 7980)

Filters Included :
Cut-Off Wavelength: [400nm](#) , [425nm](#), [450nm](#), [475nm](#),
[500nm](#), [525nm](#), [550nm](#), [575nm](#), [600nm](#), [625nm](#),
[650nm](#), [675nm](#), [700nm](#), [725nm](#), [750nm](#), [775nm](#),
[800nm](#), [825nm](#), [850nm](#), [875nm](#), [900nm](#), [925nm](#),

[950nm](#), [975nm](#), [1000nm](#), [1025nm](#), [1050nm](#), [1075nm](#), [1100nm](#)

Coating:
Hard Coated

Transmission (%):
≥91

Type:
Shortpass Filter

Number of Filters:
29.00

Coating Specification:
Surface 1: Hard Dielectric Sputtered
Surface 2: MgF₂

Wavelength Range (nm):
300 - 1530

Regulatory Compliance

RoHS:
Not Compliant

Certificate of Conformance:
[View](#)