

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Effilux High Power LED Backlights



Stock #22-098 [CONTACT US](#)



1



€750,00

ADD TO CART

Qty 1+

€750,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Operating Temperature (°C):
0 - 50

Dimensions (mm):

239 x239
Weight (g): 1900
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #15-875 Korea: Not Available China: #15-874
Active Area (mm): 200 x200
Type of Illumination: LED illumination
Uniformity (%): >90%
Manufacturer: Effilux
Geometry: Backlight
Illumination Mode: Continuous with AIC (Analog Intensity Control)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
