



NOTES:

1. SUBSTRATE:  
BOROFLOAT®
2. COATING SPECIFICATION:  
S1: Protected Aluminum (400-2000nm)  
R(AVG) >85% @ 400 - 700nm  
R(AVG) >90% @ 400 - 2000nm

3. FINE GROUND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	FINE GROUND
CLEAR APERTURE	$\varnothing 49.09$	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

**EO**® Edmund Optics®

TITLE	51mm Dia. Protected Aluminum, $\lambda/4$ Mirror		
DWG NO	33511	SHEET	1 OF 1