


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY
DIMENSIONS ARE IN mm [INCHES]

EXPANSION POWER	3X
DESIGN WAVELENGTH	1030 - 1100nm
CENTER WAVELENGTH	1064 ± 1nm
ENTRANCE BEAM MAX DIAMETER	10.00mm
INPUT APERTURE DIAMETER	11.00mm

 Edmund Optics			
TITLE	3X, 1064nm Draconis™ Nd:YAG Laser Line Beam Expander		
DWG NO	59128	REV	02