





FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2
SHAPE	PLANO	PLANO
SPECTRAL TRANSMITTANCE $t_p(\%)$	93	93
PASSBAND LIMIT 1 $\lambda_{p1}$ (nm)	400	400
CUT-OFF POSITION $\lambda_c$ (nm)	370±6	370±6
STOPBAND LIMIT $\lambda_s$ (nm)	323	323
WAVELENGTH	UV	UV
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

TITLE

Ø25.4mm, HOYA L-37 LONGPASS FILTER

DWG NO

66049

SHEET  
1 OF 1