




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

	VALUE
OPTICAL DENSITY	≥4.0
CENTER WAVELENGTH (CWL)	1300 ±2.5 nm
FULL WIDTH HALF MAX (FWHM)	12 ±2.5 nm
MINIMUM TRANSMISSION	>70 %
BLOCKING	200 - 1500nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



ALL DIMS IN

mm

TITLE

Ø25mm, 1300nm x 10nm, MOUNTED
BANDPASS FILTER

DWG NO

65788

SHEET
1 OF 1