





# TECHSPEC® ACHROMATIC LENSES

TECHSPEC® ACHROMATIC LENSES



Surface: IMA	IMA: 0.000 mm	Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
Spot Diagram		
33920 4/21/2017 Units are $\mu\text{m}$ . Field : 1 RMS radius : 161.051 GEO radius : 395.386 Scale bar : 1000	Airy Radius: 0.978 $\mu\text{m}$ .	33920.ZMX Configuration 1 of 1

33920 4/21/2017 Maximum Focal Shift Range: 116.9263 $\mu\text{m}$ Diffraction Limited Range: 4.375 $\mu\text{m}$ Pupil Zone: 0.0000	Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
33920.ZMX Configuration 1 of 1	



-Diff. Limit-Tangential     -Diff. Limit-Sagittal  
 -0.0000 (deg)-Tangential     -0.0000 (deg)-Sagittal

33920 4/21/2017 Maximum Scale: $\pm 500.000 \mu\text{m}$ . 0.486 0.588 0.656	Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
Surface: Image	33920.ZMX Configuration 1 of 1

33920 4/21/2017 Data for 0.4861 to 0.6563 $\mu\text{m}$ . Surface: Image	Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
Legend items refer to Field positions	33920.ZMX Configuration 1 of 1