NOTES:

1. SUBSTRATE MATERIAL: N-BK7

2. ROHS COMPLIANT


3. SURFACE \$1 TO BE PARALLEL WITH SURFACE \$2 TO WITHIN ≤ 3 ARCMIN

4. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 80% R ±5% @ 550nm 20% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 700 - 1100nm

5. CUT WITH 0.25mm MAXIMUM EDGE CHIP



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | S1 | \$2 | 7 | | | Edmund Opt | ics ® |
|--------------------|-------------|-------------|-----------------------------|-------------|--------|--------------------------------------|-----------------|
| SHAPE | PLANO | PLANO | | | | | |
| ANGLE OF INCIDENCE | 45° | 45° | THIRD ANGLE . PROJECTION | THIRD ANGLE | | Ø25mm, 80 R/20 T, PLATE BEAMSPLITTER | |
| SURFACE QUALITY | 60-40 | 60-40 | | 1 | | | |
| SURFACE FLATNESS | 1λ PER 25mm | 1λ PER 25mm | ALL DIMS IN | mm | DWG NO | 68422 | SHEET 1 OF 1 |