


NOTES:

1. SUBSTRATE MATERIAL:
BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
4.

FINE GROUND SURFACE
5. ROHS COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A		S1	S2	<div>DIMENSIONS ARE FOR REFERENCE ONLY</div> <div><div><div><div><div></div><div></div></div><div></div></div><div><div>Edmund Optics®</div></div></div></div>					
SHAPE		CONCAVE	PLANO						
EFFECTIVE FOCAL LENGTH		508mm	N/A						
FOCAL LENGTH TOLERANCE		±2%	N/A						
APERTURE		f/10	N/A	<div>THIRD ANGLE PROJECTION</div> <div></div>		TITLE		2" Dia, 20" FL Uncoated, Spherical Mirror	
SURFACE QUALITY		60-40							
SURFACE FLATNESS		λ/4							
BEVEL		PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	32820	SHEET 1 OF 1	

 **Edmund Optics®**