


NOTES:

1. SUBSTRATE MATERIAL:
BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
4.

FINE GROUND SURFACE
5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div>THIRD ANGLE PROJECTION</div><div></div></div>			
SHAPE	CONCAVE	PLANO				
EFFECTIVE FOCAL LENGTH	50.8mm	N/A	ALL DIMS IN	mm	TITLE	Ø1in, 2in FL UNCOATED, SPHERICAL MIRROR
FOCAL LENGTH TOLERANCE	±2%	N/A				
APERTURE	f/2	N/A	DWG NO	43338	SHEET 1 OF 1	
SURFACE QUALITY	60-40	60-40				
SURFACE FLATNESS	λ/4	λ/4	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		
BEVEL						

Edmund Optics®