




NOTES:

- 1. SUBSTRATE
CRYSTAL QUARTZ
- 2. EXTINCTION RATIO: >20,000:1
- 3. BEAM DEVIATION: <3 ARCMIN
- 4. BEAM SEPARATION (°): 1.0 - 1.5 , 1 @ 1064nm
- 5. DAMAGE THRESHOLD,
CW: > 500 MW/cm²
- 6. RoHS NOT COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



CLEAR APERTURE	Ø10
SURFACE QUALITY	20-10
TRANSMITTED WAVEFRONT	λ/4 @ 632.8nm
WAVELENGTH RANGE	200 - 2300nm



ALL DIMS IN

mm

TITLE

QUARTZ ROCHON POLARIZER

DWG NO

68824

SHEET
1 OF 1