




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SURFACE FLATNESS	$2\lambda$
PARALLELISM (arcmin)	$\leq 3.5$
CLEAR APERTURE (%)	$\geq 90$
EDGES	Chrome, Nickel, and Gold
WAVELENGTH RANGE (nm)	200 - 5500
WAVELENGTH RANGE ( $\mu\text{m}$ )	0.2 - 5.5
SOLDERABILITY	MIL-STD-883
RoHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE PROJECTION 	TITLE	15mm Diameter Uncoated, Metalized Sapphire Window		
	ALL DIMS IN	mm	DWG NO	65896