



LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R	27,91±0,028 CX		GLASS N-BK7 517/642		R	∞ PL	
Øe	8,1				Øe	8,1	
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm	
4/	-				4/	1,93'	
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)	
6/	-				6/	-	

PROTECTIVE CHAMFERS AS NEEDED				 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	9,0mm Diameter x 54,0mm FL, 980nm V-Coat, PCX Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	69537	SHEET SIZE A4	SHEET 1 OF 1