

1. SUBSTRATE:  
SCHOTT NG9

2. FINE GRIND SURFACE





3. COATING SPECIFICATION:  
S1 & S2:NONE

4. OPTICAL DENSITY: 3

5. TRANSMISSION (%): 0.1% AVERAGE FROM 400-700nm


## 6. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG9, 3.0 OD, 12.5mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16654	SHEET 1 OF 1