

NOTES:

1. SUBSTRATE:
SCHOTT NG4

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 0.6

5. TRANSMISSION (%): 25.11


6. ROHS COMPLIANT



NEUTRAL DENSITY FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	<div>THIRD ANGLE PROJECTION</div> 		TITLE	SCHOTT NG4, 0.6 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	80-50	80-50					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16663	SHEET 1 OF 1