




NOTES:

- 1. SUBSTRATE: Float Glass
- 2. COATING (APPLY ACROSS CLEAR APERTURE)  
 S1: Dielectric,  $\pm 5\%$  R/T @ 550nm  
 S2: AR 1/4 WAVE MgF2 @ 550nm

3. EDGES CUT

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                  | S1                  | S2                  |
|------------------|---------------------|---------------------|
| SHAPE            | PLANO               | PLANO               |
| SURFACE QUALITY  | 80-50               | 80-50               |
| SURFACE FLATNESS | 4 - $6\lambda$      | 4 - $6\lambda$      |
| BEVEL            | PROTECTED AS NEEDED | PROTECTED AS NEEDED |



ALL DIMS IN mm

**EO**® **Edmund Optics**®

TITLE

12.5 x 12.5mm, 50R/50T, AR Coated Plate  
Beamsplitter

DWG NO

13399

SHEET  
1 OF 1