

2021 Vision Systems Design Innovators Awards

SILVER HONOREE

Lens ennect®

Motorized FA lens that can be operated easily with a single USB cable




Remotely adjust in out-of-reach places



Make precise adjustments to lenses after installation



Changing the focus point and changeover for workpieces at different heights



Perfect for embedded systems

- → Focus, Iris, and Zoom can be controlled via USB
- Easy operation in areas where manual adjustment is not possible
- The stepping motor makes precise control possible
- Plug-and-play for easy deployment





BH series

DL0828UC-MPY						
Focal Length	8mm					
F-number	F2.8 - F16.0					
Working Distance	0.1m - Inf					
Angle of View (1/1.1")	69.4° x 53.8° (D 80.4°)					
Mount	С					
Sensor size	1/1.1"					
Resolution	12MP					
Filter size	M52 P=0.75mm					
Dimensions	φ 59.5mm x 63.3mm					
Weight	178g					

DL1224UC-MPY						
Focal Length	12mm					
F-number	F2.4 - F16.0					
Working Distance	0.1m - Inf					
Angle of View (1/1.1")	50.5° x 38.1° (D 60.2°)					
Mount	С					
Sensor size	1/1.1"					
Resolution	12MP					
Filter size	M35.5 x P0.5mm					
Dimensions	φ 59.5mm x 57.9mm					
Weight	163g					

DL1623UC-MPY							
Focal Length	16mm						
F-number	F2.3 - F16.0						
Working Distance	0.11m - Inf						
Angle of View (1/1.1")	38.9° x 29.0° (D 47.0°)						
Mount	С						
Sensor size	1/1.1"						
Resolution	12MP						
Filter size	M35.5 x P0.5mm						
Dimensions	φ 59.5mm x 59.2mm						
Weight	173g						

DL2523UC-MPY						
Focal Length	25mm					
F-number	F2.3 - F16.0					
Working Distance	0.12m - Inf					
Angle of View (1/1.1")	1.1") 253° x 18.7° (D 31.0°)					
Mount	С					
Sensor size	1/1.1"					
Resolution	12MP					
Filter size	M30.5 x P0.5mm					
Dimensions	φ 59.5mm x 56.9mm					
Weight	166g					

Focal Length	35mm
F-number	F2.5 - F16.0
Working Distance	0.16m - Inf
Angle of View (1/1.1")	18.2° x 13.4° (D 22.5°)
Mount	С
Sensor size	1/1.1"
Resolution	12MP
Filter size	M30.5 x P0.5mm
Dimensions	φ 59.5mm x 57.9mm
Weight	160g

DL5028UC-MPY							
Focal Length 50mm							
F-number	F2.8 - F16.0						
Working Distance	0.2m - Inf						
Angle of View (1/1.1")	13.2° x 9.7° (D 16.3°)						
Mount	С						
Sensor size	1/1.1"						
Resolution	12MP						
Filter size	M30.5 x P0.5mm						
Dimensions	φ 59.5mm x 58mm						
Weight	173g						

VL6Z1626UC-MPYIR						
Focal Length	16mm - 96mm					
F-number	F2.6 - F16C					
Working Distance	3m - Inf					
Angle of View (1,1")	Wide 48.1° x 35.6° (D 58.9°)					
Angle of view (1.1)	Tele 8.5° x 6.3° (D 10.4°)					
Mount	С					
Sensor size	1.1"					
Resolution	12MP					
Filter size	M67xP0.75					
Dimensions	78.2mm x 83.8 x 108.96mm					
Weight	330g					

EL6Z0915UCS-MPWIR						
Focal Length 9mm - 50mm						
F-number	F1.5 - F16C					
Working Distance	3m - Inf					
Angle of View (1/1,8")	Wide 46.1° x 26.3° (D 52.5°)					
Angle of view (1/1.0)	Tele 9.0° x 5.2° (D 10.2°)					
Mount	CS					
Sensor size	1/1.8"					
Resolution	5MP					
Filter size	*M67xP0.75 (With VM0918)					
Dimensions	78.2mm x 83.8 x 104.8mm					
Weight	299g					
(4)	T 1 70 1 1 1 1 1 1 1 1					

EL3Z0416	SUCS-MPWIR						
Focal Length	4.0mm - 10mm						
F-number	F1.6 - F16C						
Working Distance	0.2m- Inf						
Angle of View (1/1,8")	Wide 115.9° x 61.7° (D 138.1°)						
Angle of view (1/1.6)	Tele 46.0° x 25.8° (D 52.9°)						
Mount	CS						
Sensor size	1/1.8"						
Resolution	5MP						
Filter size	*M55 x P0.75 (With VM0418)						
Dimensions	φ 66mm x 59mm						
Weight	161g						

^(*) There is no filter mount on the top of the lens For using filters, please attach VM0918.

(*) There is no filter mount on the top of the lens For using filters, please attach VMO418.

RF series

TH SCHOS					
VL0826U-MPZ					
Focal Length	8mm				
F-number	F2.6 - F16.0				
Working Distance	0.1m - Inf				
Angle of View (1")	76.9° x 61.5° (D 88.8°)				
Mount	С				
Sensor size	1"				
Resolution	20MP				
Filter size	*M82 x P0.75mm (With ZM0810)				
Dimensions	φ 78mm x 52.93mm				
Weight	334g				
	\ Th i file				

(*)	There	is	no	filte	эг	mou	٦t	on	the	top	of	the	lens
	F	or	US	ine	fil	ters.	pl	eas	se a	atta	ch2	'MO	810

VL1226U-MPZ								
Focal Length	12mm							
F-number	F2.6 - F16.0							
Working Distance	0.1m - Inf							
Angle of View (1")	56.7° x 44.1° (D 67.4°)							
Mount	С							
Sensor size	1"							
Resolution	20MP							
Filter size	M46 x P0.75mm							
Dimensions	φ 75mm x 48.5mm							
Weight	273g							

VL1624U-MPZ		
Focal Length	16mm	
F-number	F2.6 - F16.0	
Working Distance	0.1m - Inf	
Angle of View (1")	43.8° x 336° (D 53.2°)	
Mount	С	
Sensor size	1"	
Resolution	20MP	
Filter size	M43 x P0.75mm	
Dimensions	φ 75mm x 52mm	
Weight	280g	

3522U-MP 7	Specifications are subject to change without notice.

VL2520U-MPZ	
Focal Length	25mm
F-number	F2.0 - F16.0
Working Distance	0.15m - Inf
Angle of View (1")	28.8° x 21.8° (D 35.5°)
Mount	С
Sensor size	1"
Resolution	20MP
Filter size	M46 x P0.75mm
Dimensions	φ 78mm x 47mm
Weight	257g

VL5024U-MPZ	
Focal Length	50mm
F-number	F2.4 - F16.0
Working Distance	0.2m - Inf
Angle of View (1")	14.6° x 11.0° (D 18.2°)
Mount	С
Sensor size	1"
Resolution	20MP
Filter size	M43 x P0.75mm
Dimensions	φ 75mm x 66.5mm
Weight	326g

Focal Length	35mm	
F-number	F2.2 - F16.0	
Working Distance	0.2m - Inf	
Angle of View (1")	20.8° x 15.7° (D 25.8°)	
Mount	С	
Sensor size	1"	
Resolution	20MP	
Filter size	M43 x P0.75mm	
Dimensions	φ 75mm x 66.1mm	
Weight	313g	
VL7531U-MPZ		
Focal Length	75mm	

VL7531U-MPZ	
Focal Length	75mm
F-number	F3.1 - F16
Working Distance	0.25m - Inf
Angle of View (1")	9.8° x 7.3° (D 12.2°)
Mount	С
Sensor size	1"
Resolution	20MP
Filter size	M43 x P0.75mm
Dimensions	φ 75mm x 87mm
Weight	TBD



