


- NOTES:
- 1. SUBSTRATE:
Magnesium Fluoride (MgF2)
 - 2. PARALLELISM:
SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO <3 ARCMIN
 - 3. COATING:
S1 & S2: NONE

4. FINE GRIND SURFACE

5. ROHS COMPLIANT



4.00±0.13

S1 S2

4


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	2λ	2λ
CLEAR APERTURE	Ø21.59	Ø21.59
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

**Edmund Optics®**

TITLE	25.4mm Dia., 4mm Thick, Uncoated, ISP Optics Magnesium Fluoride (MgF2) Window
DWG NO	24484
SHEET	4 OF 175