

[All Products](#) / [Optomechanics](#) / [Manual Translation Stages and Slides](#) / [Manual Stages and Slides](#)

Metric Z-Axis Stages



- Fine Micrometer Movement
- Available in Four Sizes
- Black Anodized Aluminum
- Locking Knob

Common Specifications


Physical & Mechanical Properties

Type of Movement:	Linear (Z)	Construction:	Aluminium Stage
Straight Line Accuracy (µm):	3	Travel Per Knob Rotation (mm):	0.5

Hardware & Interface Connectivity


Type of Drive:	Metric Micrometer
----------------	-------------------

Technical Information




#55-032

Units: mm




#55-031

Units: mm



#56-334


Units: mm



#56-335

Units: mm

Adapter Plate #58-291



Units: mm

Products

Stage Size (mm)	Type	Type of Drive	Height Adjustment (mm)	Load Capacity (kg)	Stock Number	Price	Buy
25 x 25	Metric	Metric Micrometer	±2.5	1	#56-334	€566,50 Volume Pricing	Contact Us
40 x 40	Metric	Metric Micrometer	±2.5	2	#55-031	€355,35 €592,25 Volume Pricing	1 In Stock
60 x 60	Metric	Metric Micrometer	±5	5	#55-032	€648,90 Volume Pricing	3 In Stock
80 x 80	Metric	Metric Micrometer	±5	5	#56-335	€721,00 Volume Pricing	1 In Stock
100 x 100	Metric	Metric Micrometer	±10	7	#62-298	€522,73 €1.045,45 Volume Pricing	14 In Stock
120 x 120	Metric	Metric Micrometer	±10	7	#62-299	€670,53 €1.117,55 Volume Pricing	8 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com