

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Double-Concave \(DCV\) Lenses](#)
TECHSPEC® Uncoated Double-Concave (DCV) Lenses


- Wavelength Range of 350-2200nm
- Precision Diameter and Centration Tolerances Allow for Easy OEM Integration
- Wide Variety of Diameters and Focal Lengths
- Additional AR Coating Options Available: [VIS-EXT](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#)

Common Specifications

Physical & Mechanical Properties



Bevel: Protective as needed

Optical Properties

Coating: Uncoated

Focal Length Specification Wavelength (nm):	587.6	Focal Length Tolerance (%):	±1
Surface Quality:	40-20	Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4		

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
6.00	-6.00	-6.41	Uncoated	N-SF11	#32-986	€28,84 Volume Pricing	20+ In Stock
6.00	-9.00	-9.32	Uncoated	N-BK7	#48-932	€28,84 Volume Pricing	20+ In Stock
6.00	-12.00	-12.33	Uncoated	N-BK7	#48-681	€28,84 Volume Pricing	20+ In Stock
9.00	-9.00	-9.61	Uncoated	N-SF11	#48-336	€29,87 Volume Pricing	20+ In Stock
9.00	-12.00	-12.41	Uncoated	N-SF11	#48-933	€29,87 Volume Pricing	20+ In Stock
9.00	-18.00	-18.49	Uncoated	N-BK7	#48-682	€29,87 Volume Pricing	2 In Stock
12.00	-12.00	-12.81	Uncoated	N-SF11	#32-988	€31,93 Volume Pricing	20+ In Stock
12.00	-18.00	-18.65	Uncoated	N-BK7	#48-934	€31,93 Volume Pricing	20+ In Stock
12.00	-24.00	-24.65	Uncoated	N-BK7	#48-683	€31,93 Volume Pricing	20+ In Stock
20.00	-20.00	-20.55	Uncoated	N-SF11	#32-990	€31,93 Volume Pricing	20+ In Stock
25.00	-25.00	-25.69	Uncoated	N-SF11	#32-992	€34,25 Volume Pricing	16 In Stock
25.00	-50.00	-50.82	Uncoated	N-BK7	#32-996	€34,25 Volume Pricing	Contact Us
25.00	-100.00	-101.64	Uncoated	N-BK7	#32-994	€34,25 Volume Pricing	20+ In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com