

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Visible Windows](#)

TECHSPEC® $\lambda/4$ N-BK7 Precision Windows



- Circular and Rectangular Sizes from 2mm to 200mm
- 8 Broadband Anti-Reflection Coating Options Available
- World's Largest Selection of Standard N-BK7 Windows
- Also Available with [Ultra-Thin N-BK7 Windows](#)

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Clear Aperture (%):	90
Edges:	Fine Ground	Knoop Hardness (kg/mm²):	610.00
Parallelism (arcmin):	<1	Poisson's Ratio:	0.21
Young's Modulus (GPa):	82		

Optical Properties

Abbe Number (v_d):	64.17		
Index of Refraction (n_d):	1.516	Surface Quality:	60-40

Material Properties

Density (g/cm³):	2.51
------------------------------------	------

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
2.00	-	1.00	Uncoated	#27-674	€41,72 Volume Pricing	20+ In Stock
2.50	-	1.00	Uncoated	#27-675	€44,55 Volume Pricing	4 In Stock
3.00	-	1.00	Uncoated	#27-719	€47,38 Volume Pricing	9 In Stock
4.00	-	1.00	Uncoated	#27-815	€53,05 Volume Pricing	20+ In Stock
5.00	-	1.00	Uncoated	#20-464	€61,80 Volume Pricing	20+ In Stock
5.00	-	1.00	MgF ₂ (400-700nm)	#23-355	€74,16 Volume Pricing	20+ In Stock
5.00	-	1.00	VIS-EXT (350-700nm)	#23-443	€89,61 Volume Pricing	1 In Stock
5.00	-	1.00	VIS-NIR (400-1000nm)	#23-399	€89,61 Volume Pricing	1 In Stock
5.00	-	1.00	VIS 0° (425-675nm)	#23-377	€86,01 Volume Pricing	5 In Stock
5.00	-	1.00	YAG-BBAR (500-1100nm)	#23-465	€89,61 Volume Pricing	11 In Stock
5.00	-	1.00	NIR I (600-1050nm)	#23-421	€86,01 Volume Pricing	2 In Stock
5.00	-	1.00	NIR II (750-1550nm)	#25-783	€86,01 Volume Pricing	5 In Stock
5.00	-	2.00	Uncoated	#45-573	€61,80 Volume Pricing	20+ In Stock
5.00	-	2.00	MgF ₂ (400-700nm)	#45-574	€74,16 Volume Pricing	20+ In Stock
5.00	-	2.00	VIS-EXT (350-700nm)	#13-286	€89,61 Volume Pricing	10 In Stock

5.00	-	2.00	VIS-NIR (400-1000nm)	#48-448	€89,61 Volume Pricing	9 In Stock
5.00	-	2.00	VIS 0° (425-675nm)	#47-515	€86,01 Volume Pricing	9 In Stock
5.00	-	2.00	YAG-BBAR (500-1100nm)	#13-308	€89,61 Volume Pricing	16 In Stock
5.00	-	2.00	NIR I (600-1050nm)	#83-464	€86,01 Volume Pricing	2 In Stock
5.00	-	2.00	NIR II (750-1550nm)	#25-784	€86,01 Volume Pricing	20+ In Stock
-	6.00 x 6.00	2.00	Uncoated	#29-300	€61,80 Volume Pricing	17 In Stock
9.00	-	1.00	Uncoated	#20-472	€61,80 Volume Pricing	12 In Stock
9.00	-	1.00	MgF ₂ (400-700nm)	#23-356	€74,16 Volume Pricing	1 In Stock
9.00	-	1.00	VIS-EXT (350-700nm)	#23-444	€89,61 Volume Pricing	5 In Stock
9.00	-	1.00	VIS-NIR (400-1000nm)	#23-400	€89,61 Volume Pricing	Contact Us
9.00	-	1.00	VIS 0° (425-675nm)	#23-378	€86,01 Volume Pricing	1 In Stock
9.00	-	1.00	YAG-BBAR (500-1100nm)	#23-466	€89,61 Volume Pricing	5 In Stock
9.00	-	1.00	NIR I (600-1050nm)	#23-422	€86,01 Volume Pricing	20+ In Stock
9.00	-	1.00	NIR II (750-1550nm)	#25-785	€86,01 Volume Pricing	5 In Stock
9.00	-	2.00	Uncoated	#49-121	€61,80 Volume Pricing	20+ In Stock
9.00	-	2.00	MgF ₂ (400-700nm)	#49-122	€74,16 Volume Pricing	20+ In Stock
9.00	-	2.00	VIS-EXT (350-700nm)	#13-287	€89,61 Volume Pricing	5 In Stock

9.00	-	2.00	VIS-NIR (400-1000nm)	#49-124	€89,61 Volume Pricing	20+ In Stock
9.00	-	2.00	VIS 0° (425-675nm)	#49-123	€86,01 Volume Pricing	20+ In Stock
9.00	-	2.00	YAG-BBAR (500-1100nm)	#13-309	€89,61 Volume Pricing	8 In Stock
9.00	-	2.00	NIR I (600-1050nm)	#83-465	€86,01 Volume Pricing	7 In Stock
9.00	-	2.00	NIR II (750-1550nm)	#25-786	€86,01 Volume Pricing	4 In Stock
10.00	-	1.00	Uncoated	#20-480	€61,80 Volume Pricing	20+ In Stock
10.00	-	1.00	MgF ₂ (400-700nm)	#23-357	€74,16 Volume Pricing	7 In Stock
10.00	-	1.00	VIS-EXT (350-700nm)	#23-445	€89,61 Volume Pricing	6 In Stock
10.00	-	1.00	VIS-NIR (400-1000nm)	#23-401	€89,61 Volume Pricing	3 In Stock
10.00	-	1.00	VIS 0° (425-675nm)	#23-379	€86,01 Volume Pricing	3 In Stock
10.00	-	1.00	YAG-BBAR (500-1100nm)	#23-467	€89,61 Volume Pricing	7 In Stock
10.00	-	1.00	NIR I (600-1050nm)	#23-423	€86,01 Volume Pricing	2 In Stock
10.00	-	1.00	NIR II (750-1550nm)	#25-787	€86,01 Volume Pricing	20+ In Stock
-	10.00 x 10.00	1.00	Uncoated	#20-539	€61,80 Volume Pricing	16 In Stock
-	10.00 x 10.00	1.00	MgF ₂ (400-700nm)	#23-369	€74,16 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	VIS-EXT (350-700nm)	#23-457	€89,61 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	VIS-NIR (400-1000nm)	#23-413	€89,61 Volume Pricing	1 In Stock

-	10.00 x 10.00	1.00	VIS 0° (425-675nm)	#23-391	€86,01 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	YAG-BBAR (500-1100nm)	#23-479	€89,61 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	NIR I (600-1050nm)	#23-435	€86,01 Volume Pricing	1 In Stock
-	10.00 x 10.00	1.00	NIR II (750-1550nm)	#25-788	€86,01 Volume Pricing	3 In Stock
10.00	-	2.00	Uncoated	#45-074	€61,80 Volume Pricing	20+ In Stock
10.00	-	2.00	MgF ₂ (400-700nm)	#45-256	€74,16 Volume Pricing	20+ In Stock
10.00	-	2.00	VIS-EXT (350-700nm)	#13-288	€89,61 Volume Pricing	8 In Stock
10.00	-	2.00	VIS-NIR (400-1000nm)	#45-657	€89,61 Volume Pricing	20+ In Stock
10.00	-	2.00	VIS 0° (425-675nm)	#47-516	€86,01 Volume Pricing	3 In Stock
10.00	-	2.00	YAG-BBAR (500-1100nm)	#13-310	€89,61 Volume Pricing	6 In Stock
10.00	-	2.00	NIR I (600-1050nm)	#83-466	€86,01 Volume Pricing	15 In Stock
10.00	-	2.00	NIR II (750-1550nm)	#25-789	€86,01 Volume Pricing	5 In Stock
-	10.00 x 10.00	2.00	Uncoated	#49-620	€61,80 Volume Pricing	20+ In Stock
-	10.00 x 10.00	2.00	MgF ₂ (400-700nm)	#49-623	€74,16 Volume Pricing	20+ In Stock
-	10.00 x 10.00	2.00	VIS-EXT (350-700nm)	#13-289	€89,61 Volume Pricing	8 In Stock
-	10.00 x 10.00	2.00	VIS-NIR (400-1000nm)	#49-631	€89,61 Volume Pricing	6 In Stock
-	10.00 x 10.00	2.00	VIS 0° (425-675nm)	#49-627	€86,01 Volume Pricing	5 In Stock

-	10.00 x 10.00	2.00	YAG-BBAR (500-1100nm)	#13-311	€89,61 Volume Pricing	5 In Stock
-	10.00 x 10.00	2.00	NIR I (600-1050nm)	#83-467	€86,01 Volume Pricing	1 In Stock
-	10.00 x 10.00	2.00	NIR II (750-1550nm)	#25-790	€86,01 Volume Pricing	4 In Stock
12.50	-	1.00	Uncoated	#20-491	€61,80 Volume Pricing	20+ In Stock
12.50	-	1.00	MgF ₂ (400-700nm)	#23-358	€74,16 Volume Pricing	Contact Us
12.50	-	1.00	VIS-EXT (350-700nm)	#23-446	€89,61 Volume Pricing	6 In Stock
12.50	-	1.00	VIS-NIR (400-1000nm)	#23-402	€89,61 Volume Pricing	20+ In Stock
12.50	-	1.00	VIS 0° (425-675nm)	#23-380	€86,01 Volume Pricing	3 In Stock
12.50	-	1.00	YAG-BBAR (500-1100nm)	#23-468	€89,61 Volume Pricing	1 In Stock
12.50	-	1.00	NIR I (600-1050nm)	#23-424	€86,01 Volume Pricing	4 In Stock
12.50	-	1.00	NIR II (750-1550nm)	#25-791	€86,01 Volume Pricing	5 In Stock
12.50	-	1.00	BBAR (1650-3000nm)	#70-280	€100,43 Volume Pricing	4 In Stock
12.50	-	2.00	Uncoated	#20-495	€61,80 Volume Pricing	20+ In Stock
12.50	-	2.00	MgF ₂ (400-700nm)	#23-359	€74,16 Volume Pricing	Contact Us
12.50	-	2.00	VIS-EXT (350-700nm)	#23-447	€89,61 Volume Pricing	2 In Stock
12.50	-	2.00	VIS-NIR (400-1000nm)	#23-403	€89,61 Volume Pricing	5 In Stock
12.50	-	2.00	VIS 0° (425-675nm)	#23-381	€86,01 Volume Pricing	2 In Stock

12.50	-	2.00	YAG-BBAR (500-1100nm)	#23-469	€89,61 Volume Pricing	5 In Stock
12.50	-	2.00	NIR I (600-1050nm)	#23-425	€86,01 Volume Pricing	1 In Stock
12.50	-	2.00	NIR II (750-1550nm)	#25-792	€86,01 Volume Pricing	5 In Stock
12.50	-	3.00	Uncoated	#45-075	€61,80 Volume Pricing	20+ In Stock
12.50	-	3.00	MgF ₂ (400-700nm)	#45-257	€74,16 Volume Pricing	Contact Us
12.50	-	3.00	VIS-EXT (350-700nm)	#13-290	€89,61 Volume Pricing	7 In Stock
12.50	-	3.00	VIS-NIR (400-1000nm)	#45-658	€89,61 Volume Pricing	5 In Stock
12.50	-	3.00	VIS 0° (425-675nm)	#47-517	€86,01 Volume Pricing	20+ In Stock
12.50	-	3.00	YAG-BBAR (500-1100nm)	#13-312	€89,61 Volume Pricing	11 In Stock
12.50	-	3.00	NIR I (600-1050nm)	#83-468	€86,01 Volume Pricing	14 In Stock
12.50	-	3.00	NIR II (750-1550nm)	#25-793	€86,01 Volume Pricing	11 In Stock
-	12.50 x 12.50	3.00	Uncoated	#49-621	€61,80 Volume Pricing	20+ In Stock
-	12.50 x 12.50	3.00	MgF ₂ (400-700nm)	#49-624	€74,16 Volume Pricing	20+ In Stock
-	12.50 x 12.50	3.00	VIS-EXT (350-700nm)	#13-291	€89,61 Volume Pricing	7 In Stock
-	12.50 x 12.50	3.00	VIS-NIR (400-1000nm)	#49-632	€89,61 Volume Pricing	5 In Stock
-	12.50 x 12.50	3.00	VIS 0° (425-675nm)	#49-628	€86,01 Volume Pricing	2 In Stock
-	12.50 x 12.50	3.00	YAG-BBAR (500-1100nm)	#13-313	€89,61 Volume Pricing	4 In Stock

-	12.50 x 12.50	3.00	NIR I (600-1050nm)	#83-469	€86,01 Volume Pricing	5 In Stock
-	12.50 x 12.50	3.00	NIR II (750-1550nm)	#25-794	€86,01 Volume Pricing	2 In Stock
12.70	-	3.00	Uncoated	#15-423	€61,80 Volume Pricing	20+ In Stock
12.70	-	3.00	MgF ₂ (400-700nm)	#15-427	€74,16 Volume Pricing	5 In Stock
12.70	-	3.00	VIS-EXT (350-700nm)	#15-787	€89,61 Volume Pricing	Contact Us
12.70	-	3.00	VIS-NIR (400-1000nm)	#15-435	€89,61 Volume Pricing	20+ In Stock
12.70	-	3.00	VIS 0° (425-675nm)	#15-431	€86,01 Volume Pricing	3 In Stock
12.70	-	3.00	YAG-BBAR (500-1100nm)	#15-791	€89,61 Volume Pricing	11 In Stock
12.70	-	3.00	NIR I (600-1050nm)	#15-439	€86,01 Volume Pricing	7 In Stock
12.70	-	3.00	NIR II (750-1550nm)	#25-795	€86,01 Volume Pricing	2 In Stock
15.00	-	1.00	Uncoated	#20-503	€63,86 Volume Pricing	Contact Us
15.00	-	1.00	MgF ₂ (400-700nm)	#23-360	€75,19 Volume Pricing	2 In Stock
15.00	-	1.00	VIS-EXT (350-700nm)	#23-448	€91,16 Volume Pricing	4 In Stock
15.00	-	1.00	VIS-NIR (400-1000nm)	#23-404	€91,16 Volume Pricing	Contact Us
15.00	-	1.00	VIS 0° (425-675nm)	#23-382	€87,55 Volume Pricing	3 In Stock
15.00	-	1.00	YAG-BBAR (500-1100nm)	#23-470	€91,16 Volume Pricing	4 In Stock
15.00	-	1.00	NIR I (600-1050nm)	#23-426	€87,55 Volume Pricing	2 In Stock

15.00	-	1.00	NIR II (750-1550nm)	#25-796	€87,55 Volume Pricing	5 In Stock
15.00	-	3.00	Uncoated	#45-575	€63,86 Volume Pricing	20+ In Stock
15.00	-	3.00	MgF ₂ (400-700nm)	#45-576	€75,19 Volume Pricing	20+ In Stock
15.00	-	3.00	VIS-EXT (350-700nm)	#13-292	€91,16 Volume Pricing	6 In Stock
15.00	-	3.00	VIS-NIR (400-1000nm)	#45-659	€91,16 Volume Pricing	20+ In Stock
15.00	-	3.00	VIS 0° (425-675nm)	#47-518	€87,55 Volume Pricing	20+ In Stock
15.00	-	3.00	YAG-BBAR (500-1100nm)	#13-314	€91,16 Volume Pricing	7 In Stock
15.00	-	3.00	NIR I (600-1050nm)	#83-470	€87,55 Volume Pricing	9 In Stock
15.00	-	3.00	NIR II (750-1550nm)	#25-797	€87,55 Volume Pricing	6 In Stock
20.00	-	1.00	Uncoated	#20-504	€67,98 Volume Pricing	20+ In Stock
20.00	-	1.00	MgF ₂ (400-700nm)	#23-361	€80,34 Volume Pricing	Contact Us
20.00	-	1.00	VIS-EXT (350-700nm)	#23-449	€96,31 Volume Pricing	4 In Stock
20.00	-	1.00	VIS-NIR (400-1000nm)	#23-405	€96,31 Volume Pricing	5 In Stock
20.00	-	1.00	VIS 0° (425-675nm)	#23-383	€93,73 Volume Pricing	3 In Stock
20.00	-	1.00	YAG-BBAR (500-1100nm)	#23-471	€96,31 Volume Pricing	4 In Stock
20.00	-	1.00	NIR I (600-1050nm)	#23-427	€93,73 Volume Pricing	5 In Stock
20.00	-	1.00	NIR II (750-1550nm)	#25-798	€93,73 Volume Pricing	1 In Stock

20.00	-	2.00	Uncoated	#20-507	€67,98 Volume Pricing	20+ In Stock
20.00	-	2.00	MgF ₂ (400-700nm)	#23-362	€80,34 Volume Pricing	5 In Stock
20.00	-	2.00	VIS-EXT (350-700nm)	#23-450	€96,31 Volume Pricing	4 In Stock
20.00	-	2.00	VIS-NIR (400-1000nm)	#23-406	€96,31 Volume Pricing	8 In Stock
20.00	-	2.00	VIS 0° (425-675nm)	#23-384	€93,73 Volume Pricing	6 In Stock
20.00	-	2.00	YAG-BBAR (500-1100nm)	#23-472	€96,31 Volume Pricing	8 In Stock
20.00	-	2.00	NIR I (600-1050nm)	#23-428	€93,73 Volume Pricing	1 In Stock
20.00	-	2.00	NIR II (750-1550nm)	#25-799	€93,73 Volume Pricing	3 In Stock
20.00	-	3.00	Uncoated	#45-577	€67,98 Volume Pricing	20+ In Stock
20.00	-	3.00	MgF ₂ (400-700nm)	#45-578	€80,34 Volume Pricing	3 In Stock
20.00	-	3.00	VIS-EXT (350-700nm)	#13-293	€96,31 Volume Pricing	2 In Stock
20.00	-	3.00	VIS-NIR (400-1000nm)	#45-660	€96,31 Volume Pricing	20+ In Stock
20.00	-	3.00	VIS 0° (425-675nm)	#47-519	€93,73 Volume Pricing	20+ In Stock
20.00	-	3.00	YAG-BBAR (500-1100nm)	#13-315	€96,31 Volume Pricing	4 In Stock
20.00	-	3.00	NIR I (600-1050nm)	#83-471	€93,73 Volume Pricing	20+ In Stock
20.00	-	3.00	NIR II (750-1550nm)	#25-800	€93,73 Volume Pricing	1 In Stock
25.00	-	1.00	Uncoated	#36-991	€72,10 Volume Pricing	20+ In Stock

25.00	-	1.00	MgF ₂ (400-700nm)	#36-994	€84,98 Volume Pricing	5 In Stock
25.00	-	1.00	VIS-EXT (350-700nm)	#13-294	€100,43 Volume Pricing	9 In Stock
25.00	-	1.00	VIS-NIR (400-1000nm)	#36-997	€100,43 Volume Pricing	14 In Stock
25.00	-	1.00	VIS 0° (425-675nm)	#36-996	€97,34 Volume Pricing	6 In Stock
25.00	-	1.00	YAG-BBAR (500-1100nm)	#13-316	€100,43 Volume Pricing	1 In Stock
25.00	-	1.00	NIR I (600-1050nm)	#36-995	€97,34 Volume Pricing	14 In Stock
25.00	-	1.00	NIR II (750-1550nm)	#25-801	€97,34 Volume Pricing	2 In Stock
25.00	-	1.00	BBAR (1650-3000nm)	#70-281	€109,18 Volume Pricing	3 In Stock
-	25.00 x 25.00	1.00	Uncoated	#20-556	€72,10 Volume Pricing	20+ In Stock
-	25.00 x 25.00	1.00	MgF ₂ (400-700nm)	#23-370	€84,98 Volume Pricing	4 In Stock
-	25.00 x 25.00	1.00	VIS-EXT (350-700nm)	#23-458	€100,43 Volume Pricing	Contact Us
-	25.00 x 25.00	1.00	VIS-NIR (400-1000nm)	#23-414	€100,43 Volume Pricing	6 In Stock
-	25.00 x 25.00	1.00	VIS 0° (425-675nm)	#23-392	€97,34 Volume Pricing	1 In Stock
-	25.00 x 25.00	1.00	YAG-BBAR (500-1100nm)	#23-480	€100,43 Volume Pricing	1 In Stock
-	25.00 x 25.00	1.00	NIR I (600-1050nm)	#23-436	€97,34 Volume Pricing	5 In Stock
-	25.00 x 25.00	1.00	NIR II (750-1550nm)	#25-802	€97,34 Volume Pricing	5 In Stock
25.00	-	2.00	Uncoated	#36-992	€72,10 Volume Pricing	20+ In Stock

25.00	-	2.00	MgF ₂ (400-700nm)	#36-998	€84,98 Volume Pricing	20+ In Stock
25.00	-	2.00	VIS-EXT (350-700nm)	#13-295	€100,43 Volume Pricing	10 In Stock
25.00	-	2.00	VIS-NIR (400-1000nm)	#37-002	€100,43 Volume Pricing	4 In Stock
25.00	-	2.00	VIS 0° (425-675nm)	#37-001	€97,34 Volume Pricing	7 In Stock
25.00	-	2.00	YAG-BBAR (500-1100nm)	#13-317	€100,43 Volume Pricing	6 In Stock
25.00	-	2.00	NIR I (600-1050nm)	#36-999	€97,34 Volume Pricing	11 In Stock
25.00	-	2.00	NIR II (750-1550nm)	#25-803	€97,34 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	Uncoated	#20-573	€72,10 Volume Pricing	7 In Stock
-	25.00 x 25.00	2.00	MgF ₂ (400-700nm)	#23-371	€84,98 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	VIS-EXT (350-700nm)	#23-459	€100,43 Volume Pricing	Contact Us
-	25.00 x 25.00	2.00	VIS-NIR (400-1000nm)	#23-415	€100,43 Volume Pricing	4 In Stock
-	25.00 x 25.00	2.00	VIS 0° (425-675nm)	#23-393	€97,34 Volume Pricing	4 In Stock
-	25.00 x 25.00	2.00	YAG-BBAR (500-1100nm)	#23-481	€100,43 Volume Pricing	13 In Stock
-	25.00 x 25.00	2.00	NIR I (600-1050nm)	#23-437	€97,34 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	NIR II (750-1550nm)	#25-804	€97,34 Volume Pricing	2 In Stock
25.00	-	3.00	Uncoated	#36-993	€72,10 Volume Pricing	20+ In Stock
25.00	-	3.00	MgF ₂ (400-700nm)	#37-003	€84,98 Volume Pricing	Contact Us

25.00	-	3.00	VIS-EXT (350-700nm)	#13-296	€100,43 Volume Pricing	5 In Stock
25.00	-	3.00	VIS-NIR (400-1000nm)	#37-006	€100,43 Volume Pricing	3 In Stock
25.00	-	3.00	VIS 0° (425-675nm)	#37-005	€97,34 Volume Pricing	12 In Stock
25.00	-	3.00	YAG-BBAR (500-1100nm)	#13-318	€100,43 Volume Pricing	4 In Stock
25.00	-	3.00	NIR I (600-1050nm)	#37-004	€97,34 Volume Pricing	2 In Stock
25.00	-	3.00	NIR II (750-1550nm)	#25-805	€97,34 Volume Pricing	8 In Stock
25.00	-	3.00	BBAR (1650-3000nm)	#70-282	€109,18 Volume Pricing	3 In Stock
25.00	-	4.00	Uncoated	#45-076	€72,10 Volume Pricing	20+ In Stock
25.00	-	4.00	MgF ₂ (400-700nm)	#45-258	€84,98 Volume Pricing	2 In Stock
25.00	-	4.00	VIS-EXT (350-700nm)	#13-297	€100,43 Volume Pricing	Contact Us
25.00	-	4.00	VIS-NIR (400-1000nm)	#45-661	€100,43 Volume Pricing	15 In Stock
25.00	-	4.00	VIS 0° (425-675nm)	#47-520	€97,34 Volume Pricing	20+ In Stock
25.00	-	4.00	YAG-BBAR (500-1100nm)	#13-319	€100,43 Volume Pricing	12 In Stock
25.00	-	4.00	NIR I (600-1050nm)	#83-472	€97,34 Volume Pricing	2 In Stock
25.00	-	4.00	NIR II (750-1550nm)	#25-806	€97,34 Volume Pricing	3 In Stock
-	25.00 x 25.00	4.00	Uncoated	#49-622	€72,10 Volume Pricing	20+ In Stock
-	25.00 x 25.00	4.00	MgF ₂ (400-700nm)	#49-625	€84,98 Volume Pricing	1 In Stock

-	25.00 x 25.00	4.00	VIS-EXT (350-700nm)	#13-298	€100,43 Volume Pricing	5 In Stock
-	25.00 x 25.00	4.00	VIS-NIR (400-1000nm)	#49-633	€100,43 Volume Pricing	3 In Stock
-	25.00 x 25.00	4.00	VIS 0° (425-675nm)	#49-629	€97,34 Volume Pricing	20+ In Stock
-	25.00 x 25.00	4.00	YAG-BBAR (500-1100nm)	#13-320	€100,43 Volume Pricing	6 In Stock
-	25.00 x 25.00	4.00	NIR I (600-1050nm)	#83-473	€97,34 Volume Pricing	Contact Us
-	25.00 x 25.00	4.00	NIR II (750-1550nm)	#25-807	€97,34 Volume Pricing	6 In Stock
-	25.00 x 35.00	3.00	Uncoated	#29-301	€75,19 Volume Pricing	20+ In Stock
-	25.20 x 35.60	1.00	Uncoated	#29-302	€75,19 Volume Pricing	20+ In Stock
25.40	-	1.00	Uncoated	#20-512	€72,10 Volume Pricing	Contact Us
25.40	-	1.00	MgF ₂ (400-700nm)	#23-363	€84,98 Volume Pricing	3 In Stock
25.40	-	1.00	VIS-EXT (350-700nm)	#23-451	€100,43 Volume Pricing	Contact Us
25.40	-	1.00	VIS-NIR (400-1000nm)	#23-407	€100,43 Volume Pricing	Contact Us
25.40	-	1.00	VIS 0° (425-675nm)	#23-385	€97,34 Volume Pricing	1 In Stock
25.40	-	1.00	YAG-BBAR (500-1100nm)	#23-473	€100,43 Volume Pricing	9 In Stock
25.40	-	1.00	NIR I (600-1050nm)	#23-429	€97,34 Volume Pricing	5 In Stock
25.40	-	1.00	NIR II (750-1550nm)	#25-808	€97,34 Volume Pricing	1 In Stock
25.40	-	2.00	Uncoated	#15-424	€72,10 Volume Pricing	20+ In Stock

25.40	-	2.00	MgF ₂ (400-700nm)	#15-428	€84,98 Volume Pricing	1 In Stock
25.40	-	2.00	VIS-EXT (350-700nm)	#15-788	€100,43 Volume Pricing	Contact Us
25.40	-	2.00	VIS-NIR (400-1000nm)	#15-436	€100,43 Volume Pricing	6 In Stock
25.40	-	2.00	VIS 0° (425-675nm)	#15-432	€97,34 Volume Pricing	4 In Stock
25.40	-	2.00	YAG-BBAR (500-1100nm)	#15-792	€100,43 Volume Pricing	3 In Stock
25.40	-	2.00	NIR I (600-1050nm)	#15-440	€97,34 Volume Pricing	9 In Stock
25.40	-	2.00	NIR II (750-1550nm)	#25-809	€97,34 Volume Pricing	3 In Stock
25.40	-	4.00	Uncoated	#15-425	€72,10 Volume Pricing	20+ In Stock
25.40	-	4.00	MgF ₂ (400-700nm)	#15-429	€84,98 Volume Pricing	3 In Stock
25.40	-	4.00	VIS-EXT (350-700nm)	#15-789	€100,43 Volume Pricing	5 In Stock
25.40	-	4.00	VIS-NIR (400-1000nm)	#15-437	€100,43 Volume Pricing	6 In Stock
25.40	-	4.00	VIS 0° (425-675nm)	#15-433	€97,34 Volume Pricing	3 In Stock
25.40	-	4.00	YAG-BBAR (500-1100nm)	#15-793	€100,43 Volume Pricing	3 In Stock
25.40	-	4.00	NIR I (600-1050nm)	#15-441	€97,34 Volume Pricing	4 In Stock
25.40	-	4.00	NIR II (750-1550nm)	#25-810	€97,34 Volume Pricing	5 In Stock
30.00	-	1.00	Uncoated	#20-528	€75,19 Volume Pricing	20+ In Stock
30.00	-	1.00	MgF ₂ (400-700nm)	#23-364	€95,28 Volume Pricing	1 In Stock

30.00	-	1.00	VIS-EXT (350-700nm)	#23-452	€117,42 Volume Pricing	4 In Stock
30.00	-	1.00	VIS-NIR (400-1000nm)	#23-408	€117,42 Volume Pricing	20+ In Stock
30.00	-	1.00	VIS 0° (425-675nm)	#23-386	€113,30 Volume Pricing	3 In Stock
30.00	-	1.00	YAG-BBAR (500-1100nm)	#23-474	€117,42 Volume Pricing	4 In Stock
30.00	-	1.00	NIR I (600-1050nm)	#23-430	€113,30 Volume Pricing	9 In Stock
30.00	-	1.00	NIR II (750-1550nm)	#25-811	€113,30 Volume Pricing	1 In Stock
30.00	-	2.00	Uncoated	#20-530	€75,19 Volume Pricing	20+ In Stock
30.00	-	2.00	MgF ₂ (400-700nm)	#23-365	€95,28 Volume Pricing	4 In Stock
30.00	-	2.00	VIS-EXT (350-700nm)	#23-453	€117,42 Volume Pricing	Contact Us
30.00	-	2.00	VIS-NIR (400-1000nm)	#23-409	€117,42 Volume Pricing	10 In Stock
30.00	-	2.00	VIS 0° (425-675nm)	#23-387	€113,30 Volume Pricing	8 In Stock
30.00	-	2.00	YAG-BBAR (500-1100nm)	#23-475	€117,42 Volume Pricing	2 In Stock
30.00	-	2.00	NIR I (600-1050nm)	#23-431	€113,30 Volume Pricing	5 In Stock
30.00	-	2.00	NIR II (750-1550nm)	#25-812	€113,30 Volume Pricing	7 In Stock
30.00	-	4.00	Uncoated	#45-579	€75,19 Volume Pricing	20+ In Stock
30.00	-	4.00	MgF ₂ (400-700nm)	#45-580	€95,28 Volume Pricing	14 In Stock
30.00	-	4.00	VIS-EXT (350-700nm)	#13-299	€117,42 Volume Pricing	13 In Stock

30.00	-	4.00	VIS-NIR (400-1000nm)	#48-445	€117,42 Volume Pricing	20+ In Stock
30.00	-	4.00	VIS 0° (425-675nm)	#47-521	€113,30 Volume Pricing	20+ In Stock
30.00	-	4.00	YAG-BBAR (500-1100nm)	#13-321	€117,42 Volume Pricing	20+ In Stock
30.00	-	4.00	NIR I (600-1050nm)	#83-474	€113,30 Volume Pricing	13 In Stock
30.00	-	4.00	NIR II (750-1550nm)	#25-813	€113,30 Volume Pricing	5 In Stock
-	35.00 x 35.00	1.00	Uncoated	#20-584	€83,95 Volume Pricing	14 In Stock
-	35.00 x 35.00	1.00	MgF ₂ (400-700nm)	#23-372	€103,00 Volume Pricing	Contact Us
-	35.00 x 35.00	1.00	VIS-EXT (350-700nm)	#23-460	€122,57 Volume Pricing	3 In Stock
-	35.00 x 35.00	1.00	VIS-NIR (400-1000nm)	#23-416	€122,57 Volume Pricing	Contact Us
-	35.00 x 35.00	1.00	VIS 0° (425-675nm)	#23-394	€120,51 Volume Pricing	9 In Stock
-	35.00 x 35.00	1.00	YAG-BBAR (500-1100nm)	#23-482	€122,57 Volume Pricing	3 In Stock
-	35.00 x 35.00	1.00	NIR I (600-1050nm)	#23-438	€120,51 Volume Pricing	1 In Stock
-	35.00 x 35.00	1.00	NIR II (750-1550nm)	#25-814	€120,51 Volume Pricing	5 In Stock
-	35.00 x 35.00	2.00	Uncoated	#20-586	€83,95 Volume Pricing	20+ In Stock
-	35.00 x 35.00	2.00	MgF ₂ (400-700nm)	#23-373	€103,00 Volume Pricing	3 In Stock
-	35.00 x 35.00	2.00	VIS-EXT (350-700nm)	#23-461	€122,57 Volume Pricing	11 In Stock
-	35.00 x 35.00	2.00	VIS-NIR (400-1000nm)	#23-417	€122,57 Volume Pricing	Contact Us

-	35.00 x 35.00	2.00	VIS 0° (425-675nm)	#23-395	€120,51 Volume Pricing	2 In Stock
-	35.00 x 35.00	2.00	YAG-BBAR (500-1100nm)	#23-483	€122,57 Volume Pricing	5 In Stock
-	35.00 x 35.00	2.00	NIR I (600-1050nm)	#23-439	€120,51 Volume Pricing	2 In Stock
-	35.00 x 35.00	2.00	NIR II (750-1550nm)	#25-815	€120,51 Volume Pricing	2 In Stock
-	35.00 x 35.00	3.00	Uncoated	#49-470	€83,95 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	MgF ₂ (400-700nm)	#49-626	€103,00 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	VIS-EXT (350-700nm)	#13-300	€122,57 Volume Pricing	Contact Us
-	35.00 x 35.00	3.00	VIS-NIR (400-1000nm)	#49-634	€122,57 Volume Pricing	17 In Stock
-	35.00 x 35.00	3.00	VIS 0° (425-675nm)	#49-630	€120,51 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	YAG-BBAR (500-1100nm)	#13-322	€122,57 Volume Pricing	6 In Stock
-	35.00 x 35.00	3.00	NIR I (600-1050nm)	#83-475	€120,51 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	NIR II (750-1550nm)	#25-816	€120,51 Volume Pricing	4 In Stock
40.00	-	1.00	Uncoated	#20-532	€92,70 Volume Pricing	20+ In Stock
40.00	-	1.00	MgF ₂ (400-700nm)	#23-366	€110,21 Volume Pricing	5 In Stock
40.00	-	1.00	VIS-EXT (350-700nm)	#23-454	€129,78 Volume Pricing	5 In Stock
40.00	-	1.00	VIS-NIR (400-1000nm)	#23-410	€129,78 Volume Pricing	4 In Stock
40.00	-	1.00	VIS 0° (425-675nm)	#23-388	€127,72 Volume Pricing	8 In Stock

40.00	-	1.00	YAG-BBAR (500-1100nm)	#23-476	€129,78 Volume Pricing	3 In Stock
40.00	-	1.00	NIR I (600-1050nm)	#23-432	€127,72 Volume Pricing	1 In Stock
40.00	-	1.00	NIR II (750-1550nm)	#25-817	€127,72 Volume Pricing	4 In Stock
40.00	-	2.00	Uncoated	#20-536	€92,70 Volume Pricing	11 In Stock
40.00	-	2.00	MgF ₂ (400-700nm)	#23-367	€110,21 Volume Pricing	5 In Stock
40.00	-	2.00	VIS-EXT (350-700nm)	#23-455	€129,78 Volume Pricing	1 In Stock
40.00	-	2.00	VIS-NIR (400-1000nm)	#23-411	€129,78 Volume Pricing	Contact Us
40.00	-	2.00	VIS 0° (425-675nm)	#23-389	€127,72 Volume Pricing	Contact Us
40.00	-	2.00	YAG-BBAR (500-1100nm)	#23-477	€129,78 Volume Pricing	3 In Stock
40.00	-	2.00	NIR I (600-1050nm)	#23-433	€127,72 Volume Pricing	3 In Stock
40.00	-	2.00	NIR II (750-1550nm)	#25-818	€127,72 Volume Pricing	4 In Stock
40.00	-	4.00	Uncoated	#45-581	€92,70 Volume Pricing	20+ In Stock
40.00	-	4.00	MgF ₂ (400-700nm)	#45-582	€110,21 Volume Pricing	20+ In Stock
40.00	-	4.00	VIS-EXT (350-700nm)	#13-301	€129,78 Volume Pricing	1 In Stock
40.00	-	4.00	VIS-NIR (400-1000nm)	#48-446	€129,78 Volume Pricing	20+ In Stock
40.00	-	4.00	VIS 0° (425-675nm)	#47-522	€127,72 Volume Pricing	20+ In Stock
40.00	-	4.00	YAG-BBAR (500-1100nm)	#13-323	€129,78 Volume Pricing	13 In Stock

40.00	-	4.00	NIR I (600-1050nm)	#83-476	€127,72 Volume Pricing	7 In Stock
40.00	-	4.00	NIR II (750-1550nm)	#25-819	€127,72 Volume Pricing	5 In Stock
50.00	-	1.00	Uncoated	#34-427	€97,85 Volume Pricing	20+ In Stock
50.00	-	1.00	MgF ₂ (400-700nm)	#37-007	€118,45 Volume Pricing	Contact Us
50.00	-	1.00	VIS-EXT (350-700nm)	#13-302	€134,93 Volume Pricing	3 In Stock
50.00	-	1.00	VIS-NIR (400-1000nm)	#37-010	€134,93 Volume Pricing	20+ In Stock
50.00	-	1.00	VIS 0° (425-675nm)	#37-009	€132,87 Volume Pricing	4 In Stock
50.00	-	1.00	YAG-BBAR (500-1100nm)	#13-324	€134,93 Volume Pricing	5 In Stock
50.00	-	1.00	NIR I (600-1050nm)	#37-008	€132,87 Volume Pricing	3 In Stock
50.00	-	1.00	NIR II (750-1550nm)	#25-820	€132,87 Volume Pricing	3 In Stock
50.00	-	3.00	BBAR (1650-3000nm)	#70-283	€138,02 Volume Pricing	4 In Stock
-	50.00 x 50.00	1.00	Uncoated	#20-592	€97,85 Volume Pricing	20+ In Stock
-	50.00 x 50.00	1.00	MgF ₂ (400-700nm)	#23-374	€118,45 Volume Pricing	5 In Stock
-	50.00 x 50.00	1.00	VIS-EXT (350-700nm)	#23-462	€134,93 Volume Pricing	2 In Stock
-	50.00 x 50.00	1.00	VIS-NIR (400-1000nm)	#23-418	€134,93 Volume Pricing	2 In Stock
-	50.00 x 50.00	1.00	VIS 0° (425-675nm)	#23-396	€132,87 Volume Pricing	5 In Stock
-	50.00 x 50.00	1.00	YAG-BBAR (500-1100nm)	#23-484	€134,93 Volume Pricing	4 In Stock

-	50.00 x 50.00	1.00	NIR I (600-1050nm)	#23-440	€132,87 Volume Pricing	3 In Stock
-	50.00 x 50.00	1.00	NIR II (750-1550nm)	#25-821	€132,87 Volume Pricing	3 In Stock
50.00	-	2.00	Uncoated	#34-428	€97,85 Volume Pricing	20+ In Stock
50.00	-	2.00	MgF ₂ (400-700nm)	#37-011	€118,45 Volume Pricing	2 In Stock
50.00	-	2.00	VIS-EXT (350-700nm)	#13-303	€134,93 Volume Pricing	2 In Stock
50.00	-	2.00	VIS-NIR (400-1000nm)	#37-014	€134,93 Volume Pricing	14 In Stock
50.00	-	2.00	VIS 0° (425-675nm)	#37-013	€132,87 Volume Pricing	8 In Stock
50.00	-	2.00	YAG-BBAR (500-1100nm)	#13-325	€134,93 Volume Pricing	4 In Stock
50.00	-	2.00	NIR I (600-1050nm)	#37-012	€132,87 Volume Pricing	3 In Stock
50.00	-	2.00	NIR II (750-1550nm)	#25-822	€132,87 Volume Pricing	3 In Stock
-	50.00 x 50.00	2.00	Uncoated	#20-596	€97,85 Volume Pricing	20+ In Stock
-	50.00 x 50.00	2.00	MgF ₂ (400-700nm)	#23-375	€118,45 Volume Pricing	2 In Stock
-	50.00 x 50.00	2.00	VIS-EXT (350-700nm)	#23-463	€134,93 Volume Pricing	20+ In Stock
-	50.00 x 50.00	2.00	VIS-NIR (400-1000nm)	#23-419	€134,93 Volume Pricing	2 In Stock
-	50.00 x 50.00	2.00	VIS 0° (425-675nm)	#23-397	€132,87 Volume Pricing	3 In Stock
-	50.00 x 50.00	2.00	YAG-BBAR (500-1100nm)	#23-485	€134,93 Volume Pricing	5 In Stock
-	50.00 x 50.00	2.00	NIR I (600-1050nm)	#23-441	€132,87 Volume Pricing	5 In Stock

-	50.00 x 50.00	2.00	NIR II (750-1550nm)	#25-823	€132,87 Volume Pricing	11 In Stock
50.00	-	3.00	Uncoated	#34-429	€97,85 Volume Pricing	20+ In Stock
50.00	-	3.00	MgF ₂ (400-700nm)	#37-015	€118,45 Volume Pricing	2 In Stock
50.00	-	3.00	VIS-EXT (350-700nm)	#13-304	€134,93 Volume Pricing	9 In Stock
50.00	-	3.00	VIS-NIR (400-1000nm)	#37-018	€134,93 Volume Pricing	13 In Stock
50.00	-	3.00	VIS 0° (425-675nm)	#37-017	€132,87 Volume Pricing	10 In Stock
50.00	-	3.00	YAG-BBAR (500-1100nm)	#13-326	€134,93 Volume Pricing	1 In Stock
50.00	-	3.00	NIR I (600-1050nm)	#37-016	€132,87 Volume Pricing	9 In Stock
50.00	-	3.00	NIR II (750-1550nm)	#25-824	€132,87 Volume Pricing	5 In Stock
50.00	-	4.00	Uncoated	#45-583	€97,85 Volume Pricing	20+ In Stock
50.00	-	4.00	MgF ₂ (400-700nm)	#45-584	€118,45 Volume Pricing	20+ In Stock
50.00	-	4.00	VIS-EXT (350-700nm)	#13-305	€134,93 Volume Pricing	Contact Us
50.00	-	4.00	VIS-NIR (400-1000nm)	#48-447	€134,93 Volume Pricing	20+ In Stock
50.00	-	4.00	VIS 0° (425-675nm)	#47-523	€132,87 Volume Pricing	20+ In Stock
50.00	-	4.00	YAG-BBAR (500-1100nm)	#13-327	€134,93 Volume Pricing	6 In Stock
50.00	-	4.00	NIR I (600-1050nm)	#83-477	€132,87 Volume Pricing	8 In Stock
50.00	-	4.00	NIR II (750-1550nm)	#25-825	€132,87 Volume Pricing	20+ In Stock

-	50.00 x 50.00	4.00	Uncoated	#47-944	€97,85 Volume Pricing	20+ In Stock
-	50.00 x 50.00	4.00	MgF ₂ (400-700nm)	#47-945	€118,45 Volume Pricing	1 In Stock
-	50.00 x 50.00	4.00	VIS-EXT (350-700nm)	#13-307	€134,93 Volume Pricing	8 In Stock
-	50.00 x 50.00	4.00	VIS-NIR (400-1000nm)	#47-947	€134,93 Volume Pricing	17 In Stock
-	50.00 x 50.00	4.00	VIS 0° (425-675nm)	#47-946	€132,87 Volume Pricing	7 In Stock
-	50.00 x 50.00	4.00	YAG-BBAR (500-1100nm)	#13-329	€134,93 Volume Pricing	11 In Stock
-	50.00 x 50.00	4.00	NIR I (600-1050nm)	#83-478	€132,87 Volume Pricing	14 In Stock
-	50.00 x 50.00	4.00	NIR II (750-1550nm)	#25-826	€132,87 Volume Pricing	2 In Stock
50.00	-	6.00	Uncoated	#34-430	€97,85 Volume Pricing	20+ In Stock
50.00	-	6.00	MgF ₂ (400-700nm)	#37-019	€118,45 Volume Pricing	6 In Stock
50.00	-	6.00	VIS-EXT (350-700nm)	#13-306	€134,93 Volume Pricing	5 In Stock
50.00	-	6.00	VIS-NIR (400-1000nm)	#37-022	€134,93 Volume Pricing	8 In Stock
50.00	-	6.00	VIS 0° (425-675nm)	#37-021	€132,87 Volume Pricing	3 In Stock
50.00	-	6.00	YAG-BBAR (500-1100nm)	#13-328	€134,93 Volume Pricing	11 In Stock
50.00	-	6.00	NIR I (600-1050nm)	#37-020	€132,87 Volume Pricing	5 In Stock
50.00	-	6.00	NIR II (750-1550nm)	#25-827	€132,87 Volume Pricing	4 In Stock
50.80	-	4.00	Uncoated	#15-426	€97,85 Volume Pricing	14 In Stock

50.80	-	4.00	MgF ₂ (400-700nm)	#15-430	€118,45 Volume Pricing	1 In Stock
50.80	-	4.00	VIS-EXT (350-700nm)	#15-790	€134,93 Volume Pricing	7 In Stock
50.80	-	4.00	VIS-NIR (400-1000nm)	#15-438	€134,93 Volume Pricing	5 In Stock
50.80	-	4.00	VIS 0° (425-675nm)	#15-434	€132,87 Volume Pricing	16 In Stock
50.80	-	4.00	YAG-BBAR (500-1100nm)	#15-794	€134,93 Volume Pricing	3 In Stock
50.80	-	4.00	NIR I (600-1050nm)	#15-442	€132,87 Volume Pricing	6 In Stock
50.80	-	4.00	NIR II (750-1550nm)	#25-828	€132,87 Volume Pricing	2 In Stock
75.00	-	4.00	BBAR (1650-3000nm)	#70-284	€244,11 Volume Pricing	4 In Stock
75.00	-	2.00	Uncoated	#20-538	€151,41 Volume Pricing	20+ In Stock
75.00	-	2.00	MgF ₂ (400-700nm)	#23-368	€176,13 Volume Pricing	20+ In Stock
75.00	-	2.00	VIS-EXT (350-700nm)	#23-456	€216,30 Volume Pricing	7 In Stock
75.00	-	2.00	VIS-NIR (400-1000nm)	#23-412	€216,30 Volume Pricing	Contact Us
75.00	-	2.00	VIS 0° (425-675nm)	#23-390	€211,15 Volume Pricing	2 In Stock
75.00	-	2.00	YAG-BBAR (500-1100nm)	#23-478	€216,30 Volume Pricing	15 In Stock
75.00	-	2.00	NIR I (600-1050nm)	#23-434	€211,15 Volume Pricing	4 In Stock
75.00	-	2.00	NIR II (750-1550nm)	#25-829	€211,15 Volume Pricing	9 In Stock
-	75.00 x 75.00	2.00	Uncoated	#20-598	€151,41 Volume Pricing	20+ In Stock

-	75.00 x 75.00	2.00	MgF ₂ (400-700nm)	#23-376	€176,13 Volume Pricing	5 In Stock
-	75.00 x 75.00	2.00	VIS-EXT (350-700nm)	#23-464	€216,30 Volume Pricing	5 In Stock
-	75.00 x 75.00	2.00	VIS-NIR (400-1000nm)	#23-420	€216,30 Volume Pricing	20+ In Stock
-	75.00 x 75.00	2.00	VIS 0° (425-675nm)	#23-398	€211,15 Volume Pricing	12 In Stock
-	75.00 x 75.00	2.00	YAG-BBAR (500-1100nm)	#23-486	€216,30 Volume Pricing	15 In Stock
-	75.00 x 75.00	2.00	NIR I (600-1050nm)	#23-442	€211,15 Volume Pricing	2 In Stock
-	75.00 x 75.00	2.00	NIR II (750-1550nm)	#25-830	€211,15 Volume Pricing	7 In Stock
75.00	-	4.00	Uncoated	#62-606	€151,41 Volume Pricing	20+ In Stock
75.00	-	4.00	MgF ₂ (400-700nm)	#62-608	€176,13 Volume Pricing	20+ In Stock
75.00	-	4.00	VIS-EXT (350-700nm)	#15-795	€216,30 Volume Pricing	11 In Stock
75.00	-	4.00	VIS-NIR (400-1000nm)	#84-359	€216,30 Volume Pricing	20+ In Stock
75.00	-	4.00	VIS 0° (425-675nm)	#37-070	€211,15 Volume Pricing	5 In Stock
75.00	-	4.00	YAG-BBAR (500-1100nm)	#15-797	€216,30 Volume Pricing	Contact Us
75.00	-	4.00	NIR I (600-1050nm)	#37-073	€211,15 Volume Pricing	4 In Stock
75.00	-	4.00	NIR II (750-1550nm)	#25-831	€211,15 Volume Pricing	20+ In Stock
-	75.00 x 75.00	4.00	Uncoated	#62-607	€151,41 Volume Pricing	20+ In Stock
-	75.00 x 75.00	4.00	MgF ₂ (400-700nm)	#62-609	€176,13 Volume Pricing	20+ In Stock

-	75.00 x 75.00	4.00	VIS-EXT (350-700nm)	#15-796	€216,30 Volume Pricing	20+ In Stock
-	75.00 x 75.00	4.00	VIS-NIR (400-1000nm)	#37-072	€216,30 Volume Pricing	9 In Stock
-	75.00 x 75.00	4.00	VIS 0° (425-675nm)	#37-071	€211,15 Volume Pricing	2 In Stock
-	75.00 x 75.00	4.00	YAG-BBAR (500-1100nm)	#15-798	€216,30 Volume Pricing	6 In Stock
-	75.00 x 75.00	4.00	NIR I (600-1050nm)	#37-074	€211,15 Volume Pricing	1 In Stock
-	75.00 x 75.00	4.00	NIR II (750-1550nm)	#25-832	€211,15 Volume Pricing	5 In Stock
100.00	-	6.00	Uncoated	#11-856	€222,48 Volume Pricing	20+ In Stock
-	100 x 100	6.00	Uncoated	#70-699	€222,48 Volume Pricing	Contact Us
100.00	-	6.00	MgF ₂ (400-700nm)	#11-859	€400,67 Volume Pricing	5 In Stock
100.00	-	6.00	VIS-NIR (400-1000nm)	#26-675	€540,75 Volume Pricing	Contact Us
100.00	-	6.00	VIS 0° (425-675nm)	#17-298	€520,15 Volume Pricing	7 In Stock
100.00	-	6.00	VIS-EXT (350-700nm)	#29-590	€551,05 Volume Pricing	3 In Stock
100.00	-	6.00	NIR I (600-1050nm)	#17-295	€520,15 Volume Pricing	3 In Stock
100.00	-	6.00	NIR II (750-1550nm)	#29-589	€551,05 Volume Pricing	3 In Stock
100.00	-	6.00	YAG-BBAR (500-1100nm)	#29-591	€551,05 Volume Pricing	1 In Stock
125.00	-	8.00	Uncoated	#11-857	€330,63 Volume Pricing	20+ In Stock
125.00	-	8.00	MgF ₂ (400-700nm)	#11-860	€508,82 Volume Pricing	6 In Stock

125.00	-	8.00	VIS-NIR (400-1000nm)	#26-676	€648,90 Volume Pricing	3 In Stock
125.00	-	8.00	VIS 0° (425-675nm)	#17-299	€628,30 Volume Pricing	13 In Stock
125.00	-	8.00	VIS-EXT (350-700nm)	#29-593	€664,35 Volume Pricing	Contact Us
125.00	-	8.00	NIR I (600-1050nm)	#17-296	€628,30 Volume Pricing	2 In Stock
125.00	-	8.00	NIR II (750-1550nm)	#29-592	€643,75 Volume Pricing	2 In Stock
125.00	-	8.00	YAG-BBAR (500-1100nm)	#29-594	€664,35 Volume Pricing	1 In Stock
150.00	-	10.00	Uncoated	#11-858	€470,71 Volume Pricing	5 In Stock
150.00	-	10.00	MgF ₂ (400-700nm)	#11-861	€648,90 Volume Pricing	3 In Stock
150.00	-	10.00	VIS-NIR (400-1000nm)	#26-677	€793,10 Volume Pricing	Contact Us
150.00	-	10.00	VIS 0° (425-675nm)	#17-300	€772,50 Volume Pricing	3 In Stock
150.00	-	10.00	VIS-EXT (350-700nm)	#29-596	€808,55 Volume Pricing	1 In Stock
150.00	-	10.00	NIR I (600-1050nm)	#17-297	€772,50 Volume Pricing	8 In Stock
150.00	-	10.00	NIR II (750-1550nm)	#29-595	€782,80 Volume Pricing	Contact Us
150.00	-	10.00	YAG-BBAR (500-1100nm)	#29-597	€808,55 Volume Pricing	2 In Stock
200.00	-	10.00	Uncoated	#26-475	€679,80 Volume Pricing	5 In Stock
200.00	-	10.00	MgF ₂ (400-700nm)	#29-598	€1.102,10 Volume Pricing	1 In Stock
200.00	-	10.00	VIS 0° (425-675nm)	#26-679	€1.030,00 Volume Pricing	1 In Stock

200.00	-	10.00	VIS-EXT (350-700nm)	#29-601	€1.272,05 Volume Pricing	1 In Stock
200.00	-	10.00	VIS-NIR (400-1000nm)	#29-602	€1.272,05 Volume Pricing	Contact Us
200.00	-	10.00	NIR I (600-1050nm)	#29-599	€1.215,40 Volume Pricing	3 In Stock
200.00	-	10.00	NIR II (750-1550nm)	#29-600	€1.215,40 Volume Pricing	3 In Stock
200.00	-	10.00	YAG-BBAR (500-1100nm)	#29-603	€1.272,05 Volume Pricing	2 In Stock
250.00	-	12.50	Uncoated	#29-936	€1.508,95 Volume Pricing	5 In Stock
300.00	-	15.00	Uncoated	#29-937	€1.787,05 Volume Pricing	4 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com