

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)

TECHSPEC®

λ/4 First Surface Mirrors



- Available in a Wide Range of Sizes and Shapes
- Precision Metallic Mirror Coatings
- [Contact Us](#) for Custom Sizes

Common Specifications

Physical & Mechanical Properties			
Bevel:		Protective as needed	
Edges:		Fine Ground	
Optical Properties			
Surface Flatness (P-V):		λ/4	
Substrate:		BOROFLOAT®	
Surface Quality:		60-40	
Coating Type:		Metal	

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Coating Specification	Coating	Thickness (mm)	Stock Number	Price	Buy
5.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#48-404	€54,08 Volume Pricing	20+ In Stock
5.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#48-407	€54,08 Volume Pricing	Contact Us
5.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#48-410	€70,56 Volume Pricing	20+ In Stock
5.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-186	€64,89 Volume Pricing	1 In Stock
-	$\lambda/4$	5.0 x 5.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#48-405	€54,08 Volume Pricing	20+ In Stock
-	$\lambda/4$	5.0 x 5.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#48-408	€54,08 Volume Pricing	16 In Stock
-	$\lambda/4$	5.0 x 5.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#48-411	€70,56 Volume Pricing	8 In Stock
-	$\lambda/4$	5.0 x 5.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-187	€64,89 Volume Pricing	8 In Stock
10.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-598	€54,08 Volume Pricing	5 In Stock
10.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-599	€54,08 Volume Pricing	Contact Us

10.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-600	€70,56 Volume Pricing	20+ In Stock
10.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-188	€64,89 Volume Pricing	14 In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-722	€54,08 Volume Pricing	14 In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-723	€54,08 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-724	€70,56 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-189	€64,89 Volume Pricing	Contact Us
12.50	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-601	€54,08 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-602	€54,08 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-603	€70,56 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-190	€64,89 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#48-406	€54,08 Volume Pricing	5 In Stock

-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#48-409	€54,08 Volume Pricing	14 In Stock
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#48-412	€70,56 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-191	€64,89 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#25-746	€56,65 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#25-747	€56,65 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#25-748	€75,71 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#25-749	€70,56 Volume Pricing	Contact Us
12.70	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#25-730	€54,08 Volume Pricing	Contact Us
12.70	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#25-731	€54,08 Volume Pricing	6 In Stock
12.70	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#25-732	€70,56 Volume Pricing	1 In Stock
12.70	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#25-733	€64,89 Volume Pricing	Contact Us

15.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#63-162	€56,65 Volume Pricing	17 In Stock
15.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#63-168	€56,65 Volume Pricing	1 In Stock
15.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#63-174	€75,71 Volume Pricing	20+ In Stock
15.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#88-535	€70,56 Volume Pricing	17 In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-725	€56,65 Volume Pricing	20+ In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-726	€56,65 Volume Pricing	4 In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-727	€75,71 Volume Pricing	20+ In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-192	€70,56 Volume Pricing	1 In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#30-875	€48,93 Volume Pricing	20+ In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#43-506	€56,65 Volume Pricing	14 In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#46-716	€56,65 Volume Pricing	13 In Stock

-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#32-432	€75,71 Volume Pricing	16 In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#46-721	€70,56 Volume Pricing	17 In Stock
20.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#63-163	€59,74 Volume Pricing	20+ In Stock
20.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#63-169	€59,74 Volume Pricing	1 In Stock
20.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#63-175	€78,28 Volume Pricing	2 In Stock
20.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#88-536	€73,13 Volume Pricing	9 In Stock
-	$\lambda/4$	20.0 x 20.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-728	€59,74 Volume Pricing	Contact Us
-	$\lambda/4$	20.0 x 20.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-729	€59,74 Volume Pricing	8 In Stock
-	$\lambda/4$	20.0 x 20.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-730	€78,28 Volume Pricing	20+ In Stock
-	$\lambda/4$	20.0 x 20.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-193	€73,13 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#32-454	€51,50 Volume Pricing	2 In Stock

-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#43-507	€59,74 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#46-717	€59,74 Volume Pricing	Contact Us
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-742	€78,28 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-722	€73,13 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 85\% @$ 400 - 700nm $R_{avg} > 90\% @$ 400 - 2000nm	Protected Aluminum (400- 2000nm)	5.00	#33-510	€51,50 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#32-516	€59,74 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#46-718	€59,74 Volume Pricing	Contact Us
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-433	€78,28 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-723	€73,13 Volume Pricing	15 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#45-604	€67,47 Volume Pricing	1 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#45-605	€67,47 Volume Pricing	Contact Us

25.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#45-606	€97,34 Volume Pricing	5 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#49-194	€81,37 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#30-286	€56,65 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	6.00	#45-333	€67,47 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	6.00	#45-334	€67,47 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	6.00	#45-335	€97,34 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	6.00	#49-195	€81,37 Volume Pricing	3 In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#32-513	€67,47 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#46-719	€67,47 Volume Pricing	Contact Us
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#32-434	€97,34 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#46-724	€81,37 Volume Pricing	20+ In Stock

25.40	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#25-734	€67,47 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#25-735	€67,47 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#25-736	€97,34 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#25-737	€81,37 Volume Pricing	Contact Us
30.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#63-164	€83,95 Volume Pricing	Contact Us
30.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#63-170	€83,95 Volume Pricing	9 In Stock
30.00	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#63-176	€113,30 Volume Pricing	20+ In Stock
30.00	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#88-537	€94,76 Volume Pricing	4 In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#63-165	€83,95 Volume Pricing	5 In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#63-171	€83,95 Volume Pricing	20+ In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#63-177	€113,30 Volume Pricing	5 In Stock

-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450-10000nm)	5.00	#88-538	€94,76 Volume Pricing	20+ In Stock
-	$\lambda/4$	35.0 x 50.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450-650nm)	5.00	#25-750	€105,06 Volume Pricing	5 In Stock
-	$\lambda/4$	35.0 x 50.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250-700nm)	5.00	#25-751	€105,06 Volume Pricing	7 In Stock
-	$\lambda/4$	35.0 x 50.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700-10000nm)	5.00	#25-752	€151,41 Volume Pricing	1 In Stock
-	$\lambda/4$	35.0 x 50.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450-10000nm)	5.00	#25-753	€124,63 Volume Pricing	7 In Stock
40.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450-650nm)	4.00	#63-166	€99,91 Volume Pricing	20+ In Stock
40.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250-700nm)	4.00	#63-172	€99,91 Volume Pricing	5 In Stock
40.00	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700-10000nm)	4.00	#63-178	€138,02 Volume Pricing	5 In Stock
40.00	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450-10000nm)	4.00	#88-539	€111,24 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450-650nm)	5.00	#63-167	€99,91 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250-700nm)	5.00	#63-173	€99,91 Volume Pricing	20+ In Stock

-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#63-179	€138,02 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#88-540	€111,24 Volume Pricing	5 In Stock
50.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#45-607	€113,30 Volume Pricing	15 In Stock
50.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	4.00	#45-608	€113,30 Volume Pricing	20+ In Stock
50.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	4.00	#45-609	€164,80 Volume Pricing	Contact Us
50.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	4.00	#49-196	€138,02 Volume Pricing	20+ In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	10.00	#45-336	€113,30 Volume Pricing	Contact Us
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	10.00	#45-337	€113,30 Volume Pricing	8 In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	10.00	#45-338	€164,80 Volume Pricing	1 In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	10.00	#49-197	€138,02 Volume Pricing	17 In Stock
50.80	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#25-738	€113,30 Volume Pricing	5 In Stock

50.80	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	4.00	#25-739	€113,30 Volume Pricing	4 In Stock
50.80	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	4.00	#25-740	€164,80 Volume Pricing	7 In Stock
50.80	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	4.00	#25-741	€138,02 Volume Pricing	9 In Stock
51.00	$\lambda/4$	-	$R_{avg} > 85\% @$ 400 - 700nm $R_{avg} > 90\% @$ 400 - 2000nm	Protected Aluminum (400- 2000nm)	13.00	#33-511	€64,89 Volume Pricing	Contact Us
51.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	13.00	#32-514	€113,30 Volume Pricing	2 In Stock
51.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	13.00	#46-720	€113,30 Volume Pricing	2 In Stock
51.00	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	13.00	#32-435	€164,80 Volume Pricing	20+ In Stock
51.00	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	13.00	#46-725	€138,02 Volume Pricing	4 In Stock
-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	12.00	#45-339	€219,39 Volume Pricing	14 In Stock
-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	12.00	#45-340	€219,39 Volume Pricing	8 In Stock
-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	12.00	#45-341	€294,58 Volume Pricing	5 In Stock

-	$\lambda/4$	75.0 x 75.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	12.00	#88-541	€254,41 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	15.00	#45-342	€351,23 Volume Pricing	14 In Stock
-	$\lambda/4$	100.0 x 100.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	15.00	#45-343	€351,23 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	15.00	#45-344	€484,10 Volume Pricing	5 In Stock
			R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	15.00	#88-542	€372,86 Volume Pricing	9 In Stock

Copyright 2023 | Edmund Optics, Ltd. 10000 Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com