


[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Cube Beamsplitters](#)

TECHSPEC® Cube Beamsplitters



- Multi-Layer Dielectric Coating
- Available in 30/70, 70/30, or 50/50 Split Ratios
- Optimal for Applications Insensitive to Polarization

Common Specifications



Physical & Mechanical Properties

Bevel:	Protective as needed	Construction:	Cube
---------------	----------------------	----------------------	------

Optical Properties

Beam Deviation (arcmin):	±3	Reflection/Transmission Tolerance (%):	±5
Power (fringes) @ 632.8nm:	1.25	Irregularity (fringes) @ 632.8nm:	0.25

Technical Information



Products

Dimensions (mm)	Wavelength Range (nm)	Reflection/Transmission Ratio (R/T)	Stock Number	Price	Buy
5.0 x 5.0 x 5.0	400 - 700	30/70	#68-545	€193,64 Volume Pricing	20+ In Stock
5.0 x 5.0 x 5.0	400 - 700	50/50	#32-600	€193,64 Volume Pricing	20+ In Stock
6.25 x 6.25 x 6.25	400 - 700	50/50	#45-110	€193,64 Volume Pricing	20+ In Stock
10.0 x 10.0 x 10.0	400 - 700	30/70	#68-547	€200,85 Volume Pricing	20+ In Stock
10.0 x 10.0 x 10.0	700 - 1100	50/50	#14-599	€200,85 Volume Pricing	8 In Stock
10.0 x 10.0 x 10.0	400 - 700	50/50	#32-601	€200,85 Volume Pricing	20+ In Stock
10.0 x 10.0 x 10.0	400 - 700	70/30	#68-535	€200,85 Volume Pricing	20+ In Stock
12.5 x 12.5 x 12.5	400 - 700	30/70	#68-548	€215,27 Volume Pricing	9 In Stock
12.5 x 12.5 x 12.5	400 - 700	50/50	#45-111	€215,27 Volume Pricing	20+ In Stock
12.5 x 12.5 x 12.5	400 - 700	70/30	#68-536	€215,27 Volume Pricing	7 In Stock
15.0 x 15.0 x 15.0	400 - 700	30/70	#68-549	€223,51 Volume Pricing	20+ In Stock
15.0 x 15.0 x 15.0	700 - 1100	50/50	#14-641	€223,51 Volume Pricing	17 In Stock
15.0 x 15.0 x 15.0	400 - 700	50/50	#32-503	€223,51 Volume Pricing	15 In Stock
15.0 x 15.0 x 15.0	400 - 700	70/30	#68-537	€223,51 Volume Pricing	20+ In Stock
20.0 x 20.0 x 20.0	400 - 700	30/70	#68-550	€236,90 Volume Pricing	20+ In Stock
20.0 x 20.0 x 20.0	700 - 1100	50/50	#14-642	€236,90 Volume Pricing	8 In Stock

20.0 x 20.0 x 20.0	400 - 700	50/50	#32-504	€236,90 Volume Pricing	20+ In Stock
20.0 x 20.0 x 20.0	400 - 700	70/30	#68-538	€236,90 Volume Pricing	11 In Stock
25.0 x 25.0 x 25.0	400 - 700	30/70	#68-551	€262,65 Volume Pricing	20+ In Stock
25.0 x 25.0 x 25.0	700 - 1100	50/50	#14-643	€262,65 Volume Pricing	15 In Stock
25.0 x 25.0 x 25.0	400 - 700	50/50	#32-505	€262,65 Volume Pricing	20+ In Stock
25.0 x 25.0 x 25.0	400 - 700	70/30	#68-539	€262,65 Volume Pricing	12 In Stock
30.0 x 30.0 x 30.0	400 - 700	30/70	#68-552	€297,67 Volume Pricing	8 In Stock
30.0 x 30.0 x 30.0	700 - 1100	50/50	#14-644	€297,67 Volume Pricing	12 In Stock
30.0 x 30.0 x 30.0	400 - 700	50/50	#32-701	€297,67 Volume Pricing	20+ In Stock
35.0 x 35.0 x 35.0	400 - 700	30/70	#68-553	€366,68 Volume Pricing	20+ In Stock
35.0 x 35.0 x 35.0	400 - 700	50/50	#32-702	€366,68 Volume Pricing	20+ In Stock
40.0 x 40.0 x 40.0	400 - 700	50/50	#32-506	€453,20 Volume Pricing	20+ In Stock
45.0 x 45.0 x 45.0	400 - 700	50/50	#32-703	€494,40 Volume Pricing	20+ In Stock
50.0 x 50.0 x 50.0	400 - 700	50/50	#32-704	€581,95 Volume Pricing	20+ In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com