

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Machine Vision Lasers](#)

Z-Laser Green Focusable Diode Modules

- IP67 Rated Environmentally Sealed with Simple Thread Mount
- Electrically Isolated Housing
- Focusable with Gaussian and Uniform Line Options
- 5-30V DC Operation with Reverse Polarity Protection



Common Specifications

General			
Mean Time To Failures MTTF @ 25° (hours):		Type of Laser:	
Diode		Diode	
Physical & Mechanical Properties			
Dimensions (mm):		Weight (g):	
20 Dia. x 136 L		87.00	
Housing Length (mm):		Housing Diameter (mm):	
136.00		20.00	
Optical Properties			
Wavelength (nm):		Beam Diameter (mm):	
532.00		5.00	
Color:		Focus Range (mm):	
Green		200mm to Collimation	
Electrical			
Power Stability (%):		±5%	
Hardware & Interface Connectivity			
Output Type:		Free Space	
Connector:		Input Voltage (V):	
4 Pins, M12		5 - 30 DC	
Environmental & Durability Factors			
Operating Temperature (°C):		Storage Temperature (°C):	
0 to +35		-10 to +80	

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Beam Diameter (mm)	Beam Divergence (mrad)	Fan Angle (°)	Stock Number	Price	Buy
532.00	1	5.00	<1	-	#63-872	€570,00	1 In Stock
532.00	5	5.00	<1	-	#63-873	€610,00	1 In Stock
532.00	1	5.00	<1 without Line Optics	30.00	#63-874	€610,00	Contact Us
532.00	5	5.00	<1 without Line Optics	30.00	#63-875	€635,00	Contact Us
532.00	1	5.00	<1 without Line Optics	90.00	#63-876	€650,00	Contact Us
532.00	5	5.00	<1 without Line Optics	90.00	#63-877	€635,00	Contact Us
532.00	20	5.00	<1	-	#64-824	€765,00	Contact Us
532.00	40	5.00	<1	-	#64-825	€805,00	2 In Stock
532.00	20	5.00	<1 without Line Optics	90.00	#64-826	€810,00	Contact Us
532.00	40	5.00	<1 without Line Optics	90.00	#64-827	€850,00	Contact Us
532.00	20	5.00	<1 without Line Optics	30.00	#64-828	€810,00	Contact Us
532.00	40	5.00	<1 without Line Optics	30.00	#64-829	€850,00	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com