

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

4/3" Format Fixed Focal Length Lenses



- Up to 1", C-Mount Lens
- Less than 1.0% TV Distortion
- 12mm to 50mm Focal Length

Common Specifications

General

Series: 4/3" Format Fixed Focal Length Lenses

Physical & Mechanical Properties

Iris Option: Variable

Optical Properties

Maximum Image Circle (mm): 21.60

Sensor

Maximum Sensor Format: 4/3"

Pixel Size (µm): 5.00

Threading & Mounting

Mount: C-Mount

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
12.00	4/3"	f/2 - f/22	100 - ∞	C- Mount	#86-206	€2.025,00	Contact Us
16.00	4/3"	f/2 - f/22	100 - ∞	C- Mount	#86-207	€1.915,00	Contact Us
25.00	4/3"	f/2 - f/16	150 - ∞	C- Mount	#86-208	€1.675,00	Contact Us
35.00	4/3"	f/2 - f/16	200 - ∞	C- Mount	#86-209	€1.675,00	Contact Us
50.00	4/3"	f/2 - f/22	300 - ∞	C- Mount	#86-210	€1.675,00	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com