

[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Circular Polarizers](#)

Circular Polarizers (CP42HE and CP42HER)



- Greater than 42% Transmission
- Available with Film or Plastic Substrate
- Right-Handed or Left-Handed Designs Available

Common Specifications

Optical Properties	
Transmission (%):	42
Polarization Efficiency (%):	>99.90
Environmental & Durability Factors	
Operating Temperature (°C):	-40 to +80
Heat Resistance (°C x Hours):	80 x 500

Technical Information

Products

Construction	Substrate	Dia. (mm)	Dimensions (mm)	Dimensional Tolerance (mm)	Thickness (mm)	Stock Number	Price	Buy
Circular Plastic (PMMA) Circular Polarizers	CP42HE on PMMA	12.50	-	-	2.29	#88-095	€23,69 Volume Pricing	11 In Stock
Circular Plastic (PMMA) Circular Polarizers	CP42HE on PMMA	20.00	-	-	2.29	#88-096	€30,90 Volume Pricing	11 In Stock
Circular Plastic (PMMA) Circular Polarizers	CP42HE on PMMA	25.00	-	-	2.29	#88-097	€35,02 Volume Pricing	20+ In Stock
Circular Plastic (PMMA) Circular Polarizers	CP42HE on PMMA	25.40	-	-	2.29	#88-098	€35,02 Volume Pricing	1 In Stock
Circular Plastic (PMMA) Circular Polarizers	CP42HER on PMMA	25.40	-	-	2.29	#88-101	€44,29 Volume Pricing	20+ In Stock
Circular Plastic (PMMA) Circular Polarizers	CP42HE on PMMA	50.00	-	-	2.29	#88-099	€62,83 Volume Pricing	5 In Stock
Circular Plastic (PMMA) Circular Polarizers	CP42HE on PMMA	50.80	-	-	2.29	#88-100	€62,83 Volume Pricing	14 In Stock
Circular Plastic (PMMA) Circular Polarizers	CP42HER on PMMA	50.80	-	-	2.29	#88-102	€73,13 Volume Pricing	9 In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	25.0 x 25.0	-	0.27	#29-438	€15,45 Volume Pricing	20+ In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	25.4 x 25.4	-	0.27	#29-439	€15,45 Volume Pricing	12 In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	25.4 x 25.4	-	0.27	#29-448	€15,45 Volume Pricing	20+ In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	50.0 x 50.0	-	0.27	#29-440	€27,81 Volume Pricing	20+ In Stock

Circular Polarizing Film	Polymer Film CP42HE	-	50.8 x 50.8	-	0.27	#29-441	€27,81 Volume Pricing	12 In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	50.8 x 50.8	-	0.27	#29-449	€27,81 Volume Pricing	20+ In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	100.0 x 100.0	-	0.27	#29-442	€51,50 Volume Pricing	10 In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	100.0 x 100.0	-	0.27	#29-450	€51,50 Volume Pricing	20+ In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	150.0 x 150.0	-	0.27	#29-443	€78,28 Volume Pricing	9 In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	200.0 x 200.0	-	0.27	#29-444	€114,33 Volume Pricing	15 In Stock
Circular Polarizing Film	Polymer Film CP42HER	-	250.0 x 250.0	-	0.27	#29-445	€150,38 Volume Pricing	4 In Stock
Circular Polarizing Film	Polymer Film CP42HER	-	300.0 x 300.0	-	0.27	#29-446	€278,10 Volume Pricing	3 In Stock
Circular Polarizing Film	Polymer Film CP42HER	-	300.0 x 300.0	-	0.27	#29-451	€278,10 Volume Pricing	7 In Stock
Circular Polarizing Film	Polymer Film CP42HE	-	500.0 x 600.0	-	0.27	#29-447	€421,27 Volume Pricing	8 In Stock
Circular Polarizing Film	Polymer Film CP42HER	-	500.0 x 600.0	-	0.27	#29-452	€421,27 Volume Pricing	6 In Stock

