

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

# Teledyne DALSA Genie™ Nano GigE Cameras See More by [Teledyne DALSA](#)



- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



## Common Specifications

### General

<b>Manufacturer:</b>	Teledyne DALSA	<b>Camera Series:</b>	Genie Nano-1GigE
----------------------	----------------	-----------------------	------------------

### Physical & Mechanical Properties

<b>Dimensions (mm):</b>	40.6 x 29.0 x 44.0 (includes connectors and lens mount)	<b>Weight (g):</b>	46
-------------------------	---	--------------------	----

<b>Housing:</b>	Full
-----------------	------

### Sensor

<b>Type of Sensor:</b>	Progressive Scan CMOS
------------------------	-----------------------

<b>Shutter Type:</b>	Global	<b>Exposure Time:</b>	Programmable or via external trigger
----------------------	--------	-----------------------	--------------------------------------

<b>Machine Vision Standard:</b>	GigE Vision v1.2
---------------------------------	------------------

### Electrical

<b>Power Consumption (W):</b>	3.6 - 4.6 (12VDC External Power Supply) 4.0 - 4.9 (PoE)
-------------------------------	--

### Hardware & Interface Connectivity

<b>Interface:</b>	GigE (PoE)	<b>Connector:</b>	GigE, RJ45 with Screw Locks
-------------------	------------	-------------------	-----------------------------

<b>Power Supply:</b>	Power over Ethernet (PoE) or via GPIO	<b>GPIOs:</b>	2 digital input, 2 digital output
----------------------	---------------------------------------	---------------	-----------------------------------

<b>Synchronization:</b>		Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)	<b>Interface Port Orientation:</b>		Back Panel			
<b>GPIO Connector Type:</b>		10-pin Samtec						
<b>Threading &amp; Mounting</b>								
<b>Mount:</b>		C-Mount						
<b>Mounting Threads:</b>		1/4-20 with Tripod Mount Adapter <a href="#">#34-966</a>						
<b>Environmental &amp; Durability Factors</b>								
<b>Operating Temperature (°C):</b>		-20 to +60						
<b>Storage Temperature (°C):</b>		-40 to +80						

**Technical Information**

Products

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	Stock Number	Price	Buy
Monochrome Camera	Nano-M640	1/4"	0.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-950</a>	€486,00	Contact Us
Color Camera	Nano-C640	1/4"	0.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-951</a>	€541,00	1 In Stock
Monochrome Camera	Nano-M1280	1/2"	1.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-952</a>	€546,00	3 In Stock
Color Camera	Nano-C1280	1/2"	1.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-953</a>	€583,00	Contact Us
NIR Camera	Nano-M1280 NIR	1/2"	1.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#14-675</a>	€588,00	3 In Stock
Monochrome Camera	Nano-M1920	1/1.2"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-954</a>	€567,00	3 In Stock
Color Camera	Nano-C1920	1/1.2"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-955</a>	€583,00	1 In Stock
Monochrome Camera	Nano-M1930	2/3"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-958</a>	€714,00	1 In Stock
Color Camera	Nano-C1930	2/3"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-959</a>	€761,00	1 In Stock
NIR Camera	Nano-M1930 NIR	2/3"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#14-676</a>	€866,00	1 In Stock
Monochrome Camera	Nano-M1940	1/1.2"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-956</a>	€1.003,00	3 In Stock
Color Camera	Nano-C1940	1/1.2"	2.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-957</a>	€1.019,00	1 In Stock
Monochrome Camera	Nano-M2020	1/1.8"	3.10	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-960</a>	€604,00	2 In Stock
Color Camera	Nano-C2020	1/1.8"	3.10	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-961</a>	€620,00	Contact Us

Monochrome Camera	Nano-M2420	2/3"	5.00	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-962</a>	€1.024,00	6 In Stock
Color Camera	Nano-C2420	2/3"	5.00	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-963</a>	€1.045,00	1 In Stock
Monochrome Camera	Nano-M2590	1"	5.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-964</a>	€1.061,00	2 In Stock
Color Camera	Nano-C2590	1"	5.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#34-965</a>	€1.097,00	1 In Stock
NIR Camera	Nano-M2590 NIR	1"	5.30	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#14-677</a>	€1.139,00	1 In Stock
Monochrome Camera	Nano-M4020	1.1"	12.00	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#35-911</a>	€2.436,00	1 In Stock
Color Camera	Nano-C4020	1.1"	12.00	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#35-912</a>	€2.452,00	5 In Stock
Monochrome Camera	Nano-M4040	1.1"	12.40	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#14-697</a>	€3.040,00	Contact Us
Color Camera	Nano-C4040	1.1"	12.40	GigE, RJ45 with Screw Locks	C-Mount	<a href="#">#14-698</a>	€3.334,00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
 Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)