

[All Products](#) / [Laser Optics](#) / [Laser Beam Expanders](#) / [Vega® Beam Expanders](#)

## TECHSPEC® Vega® Laser Line Beam Expanders



- AR Coated for Laser Wavelengths: 266nm, 355nm, 405nm, 532nm, 1064nm, and 1940nm
- Fixed Magnifications Available from 1.5X to 20X
- Divergence Adjustable through Rotating Optical Design

### Common Specifications

#### Optical Properties

Angle of Incidence (°): 0

Divergence Adjustment: Rotating Optics

#### Threading & Mounting

Mounting Threads:

Input: Male M30 x 1

## Technical Information

## Products

DWL (nm)	Expansion Power	Wavelength Range (nm)	Entrance Aperture (mm)	Exit Aperture (mm)	Substrate	Stock Number	Price	Buy
266	2X	250 - 280	10	23	<a href="#">Fused Silica</a>	<a href="#">#35-092</a>	€425,00 <a href="#">Volume Pricing</a>	4 In Stock
266	3X	250 - 280	10	23	<a href="#">Fused Silica</a>	<a href="#">#35-096</a>	€425,00 <a href="#">Volume Pricing</a>	3 In Stock
266	4X	250 - 280	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#19-401</a>	€441,00 <a href="#">Volume Pricing</a>	Contact Us
266	5X	250 - 280	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#35-100</a>	€545,00 <a href="#">Volume Pricing</a>	2 In Stock
266	7X	250 - 280	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#35-108</a>	€545,00 <a href="#">Volume Pricing</a>	14 In Stock
266	10X	250 - 280	7.5	32	<a href="#">Fused Silica</a>	<a href="#">#35-114</a>	€565,00 <a href="#">Volume Pricing</a>	Contact Us
355	1.5X	340 - 380	10	23	<a href="#">Fused Silica</a>	<a href="#">#12-873</a>	€395,00 <a href="#">Volume Pricing</a>	4 In Stock
355	2X	340 - 380	10	23	<a href="#">Fused Silica</a>	<a href="#">#35-093</a>	€425,00 <a href="#">Volume Pricing</a>	2 In Stock
355	3X	340 - 380	10	23	<a href="#">Fused Silica</a>	<a href="#">#35-097</a>	€425,00 <a href="#">Volume Pricing</a>	10 In Stock
355	4X	340 - 380	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#19-402</a>	€441,00 <a href="#">Volume Pricing</a>	2 In Stock
355	5X	340 - 380	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#35-101</a>	€545,00 <a href="#">Volume Pricing</a>	4 In Stock
355	7X	340 - 380	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#35-109</a>	€545,00 <a href="#">Volume Pricing</a>	1 In Stock
355	10X	340 - 380	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#35-115</a>	€565,00 <a href="#">Volume Pricing</a>	2 In Stock
355	20X	340 - 380	4.5	32	<a href="#">Fused Silica</a>	<a href="#">#35-119</a>	€905,00 <a href="#">Volume Pricing</a>	1 In Stock
405	10X	375 - 435	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#37-999</a>	€545,00 <a href="#">Volume Pricing</a>	2 In Stock
532	1.5X	500 - 570	10	23	<a href="#">Fused Silica</a>	<a href="#">#12-874</a>	€385,00 <a href="#">Volume Pricing</a>	9 In Stock
532	2X	500 - 570	10	23	<a href="#">Fused Silica</a>	<a href="#">#35-094</a>	€408,00 <a href="#">Volume Pricing</a>	Contact Us
532	3X	500 - 570	10	23	<a href="#">Fused Silica</a>	<a href="#">#35-098</a>	€408,00 <a href="#">Volume Pricing</a>	13 In Stock
532	4X	500 - 570	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#19-403</a>	€441,00 <a href="#">Volume Pricing</a>	6 In Stock

532	5X	500 - 570	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#35-102</a>	€535,00 <a href="#">Volume Pricing</a>	Contact Us
532	7X	500 - 570	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#35-112</a>	€535,00 <a href="#">Volume Pricing</a>	4 In Stock
532	10X	500 - 570	7.5	26	<a href="#">Fused Silica</a>	<a href="#">#35-116</a>	€555,00 <a href="#">Volume Pricing</a>	5 In Stock
532	20X	500 - 570	4.5	32	<a href="#">Fused Silica</a>	<a href="#">#35-120</a>	€895,00 <a href="#">Volume Pricing</a>	4 In Stock
1064	1.5X	1000 - 1140	8	23	<a href="#">Fused Silica</a>	<a href="#">#12-875</a>	€385,00 <a href="#">Volume Pricing</a>	4 In Stock
1064	2X	1000 - 1140	8	23	<a href="#">Fused Silica</a>	<a href="#">#35-095</a>	€408,00 <a href="#">Volume Pricing</a>	6 In Stock
1064	3X	1000 - 1140	8	23	<a href="#">Fused Silica</a>	<a href="#">#35-099</a>	€408,00 <a href="#">Volume Pricing</a>	8 In Stock
1064	4X	1000 - 1140	7.1	26	<a href="#">Fused Silica</a>	<a href="#">#19-404</a>	€441,00 <a href="#">Volume Pricing</a>	2 In Stock
1064	5X	1000 - 1140	7.1	26	<a href="#">Fused Silica</a>	<a href="#">#35-103</a>	€535,00 <a href="#">Volume Pricing</a>	5 In Stock
1064	7X	1000 - 1140	7.1	26	<a href="#">Fused Silica</a>	<a href="#">#35-113</a>	€535,00 <a href="#">Volume Pricing</a>	2 In Stock
1064	10X	1000 - 1140	5.45	26	<a href="#">Fused Silica</a>	<a href="#">#35-117</a>	€555,00 <a href="#">Volume Pricing</a>	1 In Stock
1064	20X	1000 - 1140	4.5	32	<a href="#">Fused Silica</a>	<a href="#">#35-121</a>	€895,00 <a href="#">Volume Pricing</a>	2 In Stock
Broadband	2X	1900 - 2100	10	23	<a href="#">Fused Silica</a>	<a href="#">#37-357</a>	€855,00 <a href="#">Volume Pricing</a>	1 In Stock
Broadband	3X	1900 - 2100	10	23	<a href="#">Fused Silica</a>	<a href="#">#37-341</a>	€855,00 <a href="#">Volume Pricing</a>	1 In Stock
Broadband	2X	1900 - 2100	10	23	<a href="#">Fused Silica</a>	<a href="#">#37-376</a>	€715,00 <a href="#">Volume Pricing</a>	3 In Stock
Broadband	3X	1900 - 2100	10	23	<a href="#">Fused Silica</a>	<a href="#">#37-377</a>	€715,00 <a href="#">Volume Pricing</a>	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
 Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)