

[All Products](#) / [Optomechanics](#) / [Benchtop Optical Mounts](#) / [Polarizer Mounts](#)

TECHSPEC® Rotation Kinematic Mounts



- 360° Continuous Optic Rotation
- 25.4mm Centerline Height
- 5° Graduations

Common Specifications

General			
Type of Optics:		Circular	
Physical & Mechanical Properties			
Construction:		Aluminum plates, stainless steel screws, and brass thread bushings	
Fine Tilt Angle (°):		±5	Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec):		4	Adjustment Screw Pitch (mm): 0.25
Min. Thickness of Compatible Optics (mm):		1.8	Pointing Stability (μrad): 1.3
Optical Properties			
Angle Tolerance (°):		0.4 per 0.25mm turn	
Threading & Mounting			
Compatible Post:		M4 x 0.7, 8-32	
Environmental & Durability Factors			
Thermal Stability (μrad):		<5	

Technical Information

Products

Size of Compatible Optics (mm)	Number of Adjustment Screws	Stock Number	Price	Buy
12.5 - 12.7	2	#36-637	€157,59 Volume Pricing	12 In Stock
25.0 - 25.4	2	#36-635	€163,00 Volume Pricing	9 In Stock
12.5 - 12.7	3	#36-638	€177,16 Volume Pricing	17 In Stock
25.0 - 25.4	3	#36-636	€185,40 Volume Pricing	15 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com