

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Backlights](#)

Advanced Illumination Medium Intensity Linear Backlights

See More by [Advanced Illumination](#)



- Intense, Diffuse Output up to 226,000 Lux
- Full Range of Wavelengths Available
- UltraSeal Washdown Backlights for Harsh Environments Also Available
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended

Common Specifications

General					
LED Lifetime (hours):		50000	Type of Illumination:	LED Illuminator	
Note:		Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	Manufacturer:	Advanced Illumination	
Geometry:		Backlight	Illumination Mode:	Constant	
Electrical					
Minimum Input Current:			0.8A		
Hardware & Interface Connectivity					
Connector:		Flying Leads			
Input Voltage (V):		24V	Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855		
Environmental & Durability Factors					
Operating Temperature (°C):		0 - 50	Environmental Rating:		IP50

Technical Information

Products

Dimensions (mm)	Color	Wavelength (nm)	Stock Number	Price	Buy
#18-644 Clearance					
					
Clearance					
216.4 x 32.2 x 21.7	IR	940.00	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€1.280,00	1 In Stock
#18-640 Clearance					
					
Clearance					
267.2 x 32.2 x 21.7	Blue	455.00	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	€985,00	Contact Us

