

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Spot Lights](#)

Advanced Illumination Ethernet Controlled High Intensity In-Line Lights

See More by [Advanced Illumination](#)



- Controllable via Ethernet GUI or Web Browser
- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Efficient Thermal Management for Long LED Life
- Compatible with [TECHSPEC® Telecentric Backlight Illuminators](#) and [Lenses](#)

Common Specifications

General			
LED Lifetime (hours):	50,000	Number of LEDs:	1
Type of Illumination:	LED Illuminator	Note:	Required Controller #18-645 ; Required Power Supply #66-855
Manufacturer:	Advanced Illumination	Geometry:	Spot Light
Illumination Mode:	Constant, Pulsed, Gated		
Physical & Mechanical Properties			
Weight (g):	85.1		
Hardware & Interface Connectivity			
Connector:	C1	Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855
Length of Cable (m):	2		
Environmental & Durability Factors			
Operating Temperature (°C):	0 to +60		

Technical Information

Products

Color	Wavelength (nm)	Stock Number	Price	Buy
UV	365.00	#21-356	€675,00	Contact Us

[#21-356-RCD-05P Recertified](#)



Recertified

Stock No.: 21-356-RCD-05P
Recertified Code: 05P (All Original
Parts Included, Perfect)

Recertified
Products

*Typically 1-2 Recertified Products are
in stock at a time. Please contact our
sales team if you would like exact
availability of an item.*

Recertified products are those
identified with the recertified logo
indicating they were returned to
Edmund Optics® and cannot be sold
as new for the following reasons:

- Open Box – Missing original packaging
- Cosmetic Blemishes – Scratches, rub marks or other minor cosmetic imperfections
- Service/Repair – Product has been serviced to the factory original specification
- Factory Returns – Product has been returned in its original condition

UV	365.00	Recertified products are inspected for damage and any necessary repairs are made. Products are then certified by Edmund Optics® to be in good working order. Since quantity is low, recertified products are sold on a first come, first serve basis. Any imperfections will be listed in the description, indicated in the stock number, and categorized by the table below. When purchasing recertified products, the Edmund	€397,80 €530,40	1 In Stock
----	--------	--	----------------------------	------------

Optics® standard [return policy](#) applies.

View all our [recertified products](#) in the Web Specials section of our website.

Parts		Cosmetic	
05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches
03	Missing Manual and Small Accessory	J	Major Defect/Scratches
02	Missing Manual and Large Accessory		

UV	395.00	#21-357	€675,00	1 In Stock
Blue	455.00	#21-358	€560,00	3 In Stock
Green	530.00	#21-359	€560,00	1 In Stock
Red	625.00	#21-360	€560,00	1 In Stock
IR	850.00	#21-361	€560,00	1 In Stock
IR	940.00	#21-362	€560,00	1 In Stock
White	-	#21-363	€560,00	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com