

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Backlights](#)

## Effilux High Power LED Backlights



- >90% Uniformity
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light

### Common Specifications

#### General

<b>Type of Illumination:</b>	LED illumination	<b>Uniformity (%):</b>	>90%
<b>Manufacturer:</b>	Effilux	<b>Geometry:</b>	Backlight
<b>Illumination Mode:</b>	Continuous with AIC (Analog Intensity Control)		

#### Hardware & Interface Connectivity

##### Power Supply:

Power Supply Required and Sold Separately:

USA: [#15-874](#)

Europe: [#15-875](#)

Japan: [#73-409](#)

Korea: [#73-409](#)

China: [#15-874](#)

#### Environmental & Durability Factors

<b>Operating Temperature (°C):</b>	0 - 50
------------------------------------	--------

## Technical Information

## Products

Color	Active Area (mm)	Stock Number	Price	Buy
White	200 x 200	<a href="#">#22-098</a>	€750,00	1 In Stock
Red	200 x 200	<a href="#">#22-099</a>	€750,00	1 In Stock
Blue	200 x 200	<a href="#">#22-100</a>	€750,00	Contact Us
White	300 x 300	<a href="#">#22-101</a>	€1.235,00	Contact Us
Red	300 x 300	<a href="#">#22-102</a>	€1.235,00	Contact Us
Blue	300 x 300	<a href="#">#22-103</a>	€1.235,00	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)