

[All Products](#) / [Optomechanics](#) / [Motorized Translation Stages](#) / [Motorized Rotary Stages](#)

Compact Motorized Rotation Stages



- Compact Footprint and Economic Price Point
- Light-weight Housing with Durable Stage Platform
- Compatible with [TECHSPEC Stages](#)
- Use Power Supply [#21-075](#) to Power Controller [#23-931](#)

Common Specifications

General			
Note:		Controller Required: #23-931	Type of Motor: Stepper Motor
Physical & Mechanical Properties			
Type of Movement:		Rotary	Guide System: Ball Bearing
Travel (°):		360	Accuracy (°): 0.03
Backlash (°):		0.2	Construction: Aluminum, 3D Printed Plastic
Height (mm):		44.7	Load Capacity (kg): 0.5
Repeatability (°):		0.03	Speed (°/s): 240
Weight (kg):		0.25	Table Diameter (mm): 70
Parallelism (°):		0.0083	Min. Incremental Movement (°): 0.02
Optical Properties			
Resolution (µm):		0.02°	
Electrical			
Maximum Operating Current (mA):		500	
Hardware & Interface Connectivity			
Type of Drive:		Gear Transmission	Computer Interface: USB-C
Environmental & Durability Factors			
Operating Temperature (°C):		10-40	

Technical Information

Products

Table Diameter (mm)	Type	Travel (°)	Stock Number	Price	Buy
70	Metric	360	#23-929	€937,30	4 In Stock
70	English	360	#23-930	€937,30	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com