

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Ultrafast Laser Mirrors](#)

TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors



- GDD as Low as $\pm 20\text{fs}^2$ at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers

Common Specifications

Physical & Mechanical Properties

Back Surface: Commercial Polish

Clear Aperture (%): 90

Optical Properties

Angle of Incidence (°): 45

Coating Type: Dielectric

Surface Quality: 10-5

Environmental & Durability Factors

Durability: MIL-PRF-13830B

Technical Information

Products

DWL (nm)	Wavelength Range (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
400	380 - 420	12.70	6.35	45	#26-823	€97,85 Volume Pricing	14 In Stock
400	380 - 420	25.40	6.35	45	#26-824	€164,80 Volume Pricing	3 In Stock
400	380 - 420	50.80	9.53	45	#26-825	€309,00 Volume Pricing	Contact Us
460	440 - 480	12.70	6.35	45	#26-826	€97,85 Volume Pricing	7 In Stock
460	440 - 480	25.40	6.35	45	#26-827	€164,80 Volume Pricing	Contact Us
460	440 - 480	50.80	9.53	45	#26-828	€309,00 Volume Pricing	9 In Stock
515	480 - 530	12.70	6.35	45	#25-092	€97,85 Volume Pricing	20+ In Stock
515	480 - 530	25.40	6.35	45	#25-093	€164,80 Volume Pricing	20+ In Stock
515	480 - 530	50.80	9.53	45	#25-094	€309,00 Volume Pricing	13 In Stock
800	750 - 850	12.70	6.35	45	#26-829	€97,85 Volume Pricing	12 In Stock
800	750 - 850	25.40	6.35	45	#26-830	€164,80 Volume Pricing	7 In Stock
800	750 - 850	50.80	9.53	45	#26-831	€309,00 Volume Pricing	20+ In Stock
920	870 - 970	12.70	6.35	45	#26-832	€97,85 Volume Pricing	20+ In Stock
920	870 - 970	25.40	6.35	45	#26-833	€164,80 Volume Pricing	Contact Us
920	870 - 970	50.80	9.53	45	#26-834	€309,00 Volume Pricing	9 In Stock
1030	990 - 1070	12.70	6.35	45	#26-835	€97,85 Volume Pricing	7 In Stock
1030	990 - 1070	25.40	6.35	45	#26-836	€164,80 Volume Pricing	Contact Us

1030	990 - 1070	50.80	9.53	45	#26-837	€309,00 Volume Pricing	2 In Stock
1060	1010 - 1110	12.70	6.35	45	#26-838	€97,85 Volume Pricing	20+ In Stock
1060	1010 - 1110	25.40	6.35	45	#26-839	€164,80 Volume Pricing	20+ In Stock
1060	1010 - 1110	50.80	9.53	45	#26-840	€309,00 Volume Pricing	11 In Stock
1310	1260 - 1360	12.70	6.35	45	#28-995	€149,35 Volume Pricing	14 In Stock
1310	1260 - 1360	25.40	6.35	45	#28-996	€211,15 Volume Pricing	Contact Us
1310	1260 - 1360	50.80	9.53	45	#28-997	€350,20 Volume Pricing	8 In Stock
1550	1510 - 1590	12.70	6.35	45	#26-841	€97,85 Volume Pricing	11 In Stock
1550	1510 - 1590	25.40	6.35	45	#26-842	€164,80 Volume Pricing	20+ In Stock
1550	1510 - 1590	50.80	9.53	45	#26-843	€309,00 Volume Pricing	1 In Stock
2000	1900 - 2100	12.70	6.35	45	#26-844	€154,50 Volume Pricing	4 In Stock
2000	1900 - 2100	25.40	6.35	45	#26-845	€221,45 Volume Pricing	20+ In Stock
2000	1900 - 2100	50.80	9.53	45	#26-846	€365,65 Volume Pricing	20+ In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com