

NIR Wire Grid Polarizers



- Designed for 700 - 2500nm
- High Transmission and High Contrast Versions Available
- Ideal for Thermal Imaging

Common Specifications

Physical & Mechanical Properties

Construction:	Wire Grid
---------------	-----------

Optical Properties

Angle of Incidence (°):	0° ±20°		
Coating:	Uncoated	Substrate:	Wire Grid on Display Grade Glass
Surface Quality:	80-50	Wavelength Range (nm):	700 - 2500

Material Properties

Thermal Expansion:	31.7 x 10-7/°C (0 - 300°C)
--------------------	----------------------------

Technical Information

Products

Thickness (mm)	Dia. (mm)	Dimensions (mm)	Mount	Extinction Ratio	Transmission (%)	Stock Number	Price	Buy
#26-993 Clearance								
								
Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
5.80	12.50	-	Mounted	1100:1@900nm 3000:1@1400nm 5500:1@1900nm 5900:1@2400nm	>81.5@900nm >87.7@1400nm >88.9@1900nm >88.6@2400nm		€746,75 Volume Pricing	1 In Stock
#26-994								
5.80	25.00	-	Mounted	1100:1@900nm 3000:1@1400nm 5500:1@1900nm 5900:1@2400nm	>81.5@900nm >87.7@1400nm >88.9@1900nm >88.6@2400nm		€921,85 Volume Pricing	3 In Stock
#26-995 Clearance								
								
Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
5.80	-	25 x 25	Mounted	1100:1@900nm 3000:1@1400nm 5500:1@1900nm 5900:1@2400nm	>81.5@900nm >87.7@1400nm >88.9@1900nm >88.6@2400nm		€818,85 Volume Pricing	2 In Stock
#26-996								
5.80	50.00	-	Mounted	1100:1@900nm 3000:1@1400nm 5500:1@1900nm 5900:1@2400nm	>81.5@900nm >87.7@1400nm >88.9@1900nm >88.6@2400nm		€1.833,40 Volume Pricing	1 In Stock
#26-997								
1.53	-	50 x 35	Unmounted	1100:1@900nm 3000:1@1400nm 5500:1@1900nm 5900:1@2400nm	>81.5@900nm >87.7@1400nm >88.9@1900nm >88.6@2400nm		€1.472,90 Volume Pricing	1 In Stock

[#26-999 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

5.80	25.00	-	Mounted	150:1@900nm >88.1@900nm 500:1@1400nm >91.0@1400nm 800:1@1900nm >91.3@1900nm 1000:1@2400nm >90.3@2400nm	€921,85 Volume Pricing	2 In Stock
------	-------	---	---------	---	---	------------

[#27-000 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

5.80	-	25 x 25	Mounted	150:1@900nm >88.1@900nm 500:1@1400nm >91.0@1400nm 800:1@1900nm >91.3@1900nm 1000:1@2400nm >90.3@2400nm	€818,85 Volume Pricing	20+ In Stock
------	---	---------	---------	---	---	--------------

5.80	50.00	-	Mounted	150:1@900nm >88.1@900nm 500:1@1400nm >91.0@1400nm 800:1@1900nm >91.3@1900nm 1000:1@2400nm >90.3@2400nm	#27-003 €1.833,40 Volume Pricing	1 In Stock
------	-------	---	---------	---	--	------------

[#27-004 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

1.53	-	50 x 35	Unmounted	150:1@900nm >88.1@900nm 500:1@1400nm >91.0@1400nm 800:1@1900nm >91.3@1900nm 1000:1@2400nm >90.3@2400nm	€1.472,90 Volume Pricing	2 In Stock
------	---	---------	-----------	---	---	------------



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com