

[All Products](#) /
 [Optics](#) /
 [Optical Filters](#) /
 [Machine Vision Filters](#) /
 [Color Filters](#)

C-Mount Camera Imaging Filters



- Threads Directly between a Lens and any C-Mount Camera
- Narrow UV, VIS and SWIR Bandpass Filters Available
- Recommended for Wide Angle Lenses
- UV Protective Windows Available

Common Specifications

Physical & Mechanical Properties

Clear Aperture CA (mm):	19.50	Outer Diameter (mm):	25.40
Construction:	Mounted in Black Anodized Ring	Substrate Thickness (mm):	1.00

Optical Properties

Surface Quality:	40-20
------------------	-------

Threading & Mounting

Filter Thread:	C-Mount
Mount Thickness (mm):	3.00

Technical Information

Products

Type	Color	Transmission Wavelength (nm)	Minimum Transmission (%)	FWHM (nm)	Cut-On Wavelength (nm)	Stock Number	Price	Buy
Narrow Bandpass Filter	Blue	460 - 490	≥85	45.00	-	#73-317	€228,66 Volume Pricing	Contact Us
Narrow Bandpass Filter	Green	525 - 550	≥85	55.00	-	#73-319	€228,66 Volume Pricing	5 In Stock
Interference Bandpass Filter	Light Red	625 - 645	≥85	28.00	-	#73-320	€257,50 Volume Pricing	Contact Us
Interference Bandpass Filter	Near-IR	845 - 860	≥88	33.00	-	#73-321	€257,50 Volume Pricing	1 In Stock
Interference Bandpass Filter	Near-IR	930 - 952	>85	32.00	-	#73-322	€257,50 Volume Pricing	Contact Us
SWIR Bandpass Filter	SWIR	1290 - 1310	≥90	35.00	-	#73-323	€353,29 Volume Pricing	Contact Us
SWIR Bandpass Filter	SWIR	1440 - 1460	≥90	35.00	-	#73-325	€353,29 Volume Pricing	Contact Us
SWIR Bandpass Filter	SWIR	1540 - 1560	>90	35.00	-	#73-326	€353,29 Volume Pricing	Contact Us
Protective Window	UV	350 - 1100	≥98	-	285.00	#73-313	€92,70 Volume Pricing	4 In Stock
Protective Window	UV	350 - 800	≥98	-	340.00	#73-314	€92,70 Volume Pricing	Contact Us
Protective Window	UV	415 - 1100	≥95	-	415.00	#73-315	€92,70 Volume Pricing	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com