

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Bar Lights](#)

Effilux SWIR LED Bar Lights



- Full Range of SWIR Wavelengths Available
- High Intensity and Uniform Lighting
- Adjustable Illumination Angles

Common Specifications

General			
Number of LEDs:	5	Type of Illumination:	LED Illuminator
Manufacturer:	Effilux	Geometry:	Bar Light
Illumination Mode:	Strobed or Constant		

Physical & Mechanical Properties	
Dimensions (mm):	51.0 W x 135.0 L x 49.0 H
Weight (g):	360

Optical Properties	
Color:	SWIR

Hardware & Interface Connectivity				
Connector:		M12, 4 pins	Input Voltage (V):	24V DC
Power Supply:		Power Supply Required and Sold Separately: USA: #15-874 Europe: #15-875 Japan: #73-409 Korea: #73-409 China: #15-874		

Threading & Mounting	
Mount:	2 Rails (1 for M6 T-Nuts)

Environmental & Durability Factors			
Operating Temperature (°C):	0 to 50	Environmental Rating:	IP50

Technical Information

Products

Title	Stock Number	Price	Buy
SWIR 1050nm Adjustable Bar Light	#28-616	€1.350,00	Contact Us
SWIR 1200nm Adjustable Bar Light	#28-617	€1.350,00	Contact Us
SWIR 1300nm Adjustable Bar Light	#28-618	€1.350,00	Contact Us
SWIR 1450nm Adjustable Bar Light	#28-619	€1.350,00	1 In Stock
SWIR 1550nm Adjustable Bar Light	#28-620	€1.350,00	2 In Stock
SWIR 1650nm Adjustable Bar Light	#28-621	€1.350,00	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com