

[See all 12 Products in Family](#)

# (0-1" Range), 0.0001", Uni-Mike Mechanical Outside Micrometer, Interchangeable Anvils

See More by [Mitutoyo](#)



Stock #78-306 **1 In Stock**

€301<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | €301,00 each                  |
| Need More? | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

#### Product Downloads

±0.002      Accuracy (inches):

#### General

0 - 1 inches      Range:

117-107      Model Number:

## Physical & Mechanical Properties

Graduation (inches):

0.0001

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.