

[See all 12 Products in Family](#)

(0-6" Range), 0.0001", Mechanical Outside Micrometer, Set of 6

See More by [Mitutoyo](#)



Stock **#78-304** **1 In Stock**

-

1

+

€1.155⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.155,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads	
±0.001	Accuracy (inches):
General	
0 - 6 inches	Range:
103-907-40	Model Number:
Contents of Kit:	

Outside Micrometer with Friction Thimble: 0-1"
Outside Micrometer with Friction Thimble: 1-2"
Outside Micrometer with Ratchet Stop: 2-3"
Outside Micrometer with Ratchet Stop: 3-4"
Outside Micrometer with Ratchet Stop: 4-5"
Outside Micrometer with Ratchet Stop: 5-6"

Physical & Mechanical Properties

0.0001Graduation (inches):

Regulatory Compliance

ViewCertificate of Conformance:

Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.